

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364977

Luminaire Tested: **FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-LI-BTR94**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364977
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-27)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-LI-BTR94
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM GLASS, TEMPERED CLEAR 0.187", 5000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4172.9 lumens
Efficiency: N/A
Efficacy: 75.7 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 55.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364977

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-LI-BTR94

Luminous Intensity Polar Plot





TEST NUMBER: P364977

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-LI-BTR94

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94	92	90	88
3	104	98	93	90	102	96	92	89	94	90	87		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	91	82	77	73	89	82	76	73	80	76	72		79	75	72		77	74	71	70
7	87	78	73	69	85	77	72	68	76	72	68		75	71	68		74	70	67	66
8	83	74	69	65	82	74	68	65	73	68	64		72	67	64		71	67	64	63
9	79	71	65	61	78	70	65	61	69	64	61		68	64	61		67	64	61	59
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	467088
5°	454719
10°	420323
15°	374189
20°	315136
25°	251122
30°	175899
35°	74508
40°	25994
45°	7129
50°	3620
55°	3383
60°	3365
65°	3067
70°	3015
75°	3984
80°	5195
85°	7394



TEST NUMBER: P364977

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-LI-BTR94

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	586.6	14.1
10°-20°	1395.5	33.4
20°-30°	1435.5	34.4
30°-40°	613.1	14.7
40°-50°	76.5	1.8
50°-60°	24.4	0.6
60°-70°	18.1	0.4
70°-80°	14.5	0.3
80°-90°	8.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3417.6	81.9
0°-40°	4030.7	96.6
0°-60°	4131.7	99.0
0°-90°	4172.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4172.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6523	
5°	6326	587
15°	5048	1396
25°	3179	1436
35°	852	613
45°	70	77
55°	27	24
65°	18	18
75°	14	15
85°	9	9
90°	0	



TEST NUMBER: P364977

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-LI-BTR94

CANDELA DISTRIBUTION (FULL):

0°	
0°	6523.4
2.5°	6471.0
5°	6326.5
7.5°	6095.4
10°	5781.1
12.5°	5430.8
15°	5047.9
17.5°	4592.8
20°	4135.8
22.5°	3666.3
25°	3178.6
27.5°	2663.9
30°	2127.5
32.5°	1511.7
35°	852.4
37.5°	487.6
40°	278.1
42.5°	144.5
45°	70.4
47.5°	37.9
50°	32.5
52.5°	28.9
55°	27.1
57.5°	25.3
60°	23.5
62.5°	19.9
65°	18.1
67.5°	16.3
70°	14.4
72.5°	14.4
75°	14.4
77.5°	12.6
80°	12.6
82.5°	10.8
85°	9.0
87.5°	5.4
90°	0.0

(END OF REPORT)