

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365018

Luminaire Tested: **FLD6BX60D010TE-FEU6B67-8035-F6LBXVM1-LI-BL87**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365018
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-43)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX60D010TE-FEU6B67-8035-F6LBXVM1-LI-BL87
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, SPECULAR CLEAR REFLECTOR,
BOTTOM LENS POLYCARBONATE, CLEAR 0.375", 6000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5103.0 lumens
Efficiency: N/A
Efficacy: 87.8 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.82
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 58.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365018

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8035-F6LBXVM1-LI-BL87

Luminous Intensity Polar Plot





TEST NUMBER: P365018

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8035-F6LBXVM1-LI-BL87

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88
3	103	97	93	89	101	96	92	88	93	90	87	91	88	85	89	86	84	83
4	99	91	86	82	97	90	85	82	88	84	81	86	83	80	84	81	79	77
5	94	86	80	76	92	85	80	76	83	79	75	82	78	75	80	77	74	73
6	90	81	75	71	88	80	75	71	79	74	71	77	73	70	76	73	70	68
7	85	77	71	67	84	76	71	67	75	70	66	74	69	66	72	69	66	64
8	82	72	67	63	80	72	67	63	71	66	63	70	65	62	69	65	62	61
9	78	69	63	59	77	68	63	59	67	62	59	66	62	59	66	62	59	57
10	74	65	60	56	74	65	60	56	64	59	56	63	59	56	63	58	56	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	196334
5°	192601
10°	177864
15°	158494
20°	135357
25°	113679
30°	89239
35°	46244
40°	22083
45°	8692
50°	2290
55°	643
60°	421
65°	375
70°	303
75°	401
80°	299
85°	595



TEST NUMBER: P365018

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8035-F6LBXVM1-LI-BL87

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	651.3	12.8
10°-20°	1557.7	30.5
20°-30°	1719.8	33.7
30°-40°	946.4	18.5
40°-50°	200.0	3.9
50°-60°	16.9	0.3
60°-70°	5.2	0.1
70°-80°	3.8	0.1
80°-90°	1.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3928.8	77.0
0°-40°	4875.2	95.5
0°-60°	5092.2	99.8
0°-90°	5103.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5103.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7188	
5°	7024	651
15°	5605	1558
25°	3772	1720
35°	1387	946
45°	225	200
55°	14	17
65°	6	5
75°	4	4
85°	2	2
90°	0	



TEST NUMBER: P365018

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8035-F6LBXVM1-LI-BL87

CANDELA DISTRIBUTION (FULL):

	0°
0°	7187.7
2.5°	7183.8
5°	7024.2
7.5°	6778.0
10°	6412.6
12.5°	6049.0
15°	5604.7
17.5°	5152.7
20°	4656.5
22.5°	4221.8
25°	3771.8
27.5°	3337.1
30°	2829.3
32.5°	2160.0
35°	1386.8
37.5°	934.8
40°	619.3
42.5°	386.6
45°	225.0
47.5°	115.4
50°	53.9
52.5°	23.1
55°	13.5
57.5°	9.6
60°	7.7
62.5°	5.8
65°	5.8
67.5°	3.8
70°	3.8
72.5°	5.8
75°	3.8
77.5°	1.9
80°	1.9
82.5°	1.9
85°	1.9
87.5°	1.9
90°	0.0

(END OF REPORT)