

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366413

Luminaire Tested: **FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-WMH-BTR86**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P366413  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-30)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-WMH-BTR86  
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, WARM HAZE REFLECTOR,  
BOTTOM TRIM POLYCARBONATE, CLEAR 0.250", 5000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3867.0 lumens  
Efficiency: N/A  
Efficacy: 70.2 lumens/watt  
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.8  
Luminous Opening: Circular (Dia: 0.44' x H: 0')  
CIE Type: Direct


Input Watts (W): 55.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P366413

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-WMH-BTR86

### Luminous Intensity Polar Plot





TEST NUMBER: P366413

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-WMH-BTR86

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	92	90	88
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	84	83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	80	78
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74
6	90	82	76	72	89	81	76	72	80	75	72	78	74	71	77	74	71	69
7	86	78	72	68	85	77	72	68	76	71	68	75	70	67	73	70	67	66
8	82	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62
9	79	70	64	61	78	69	64	61	69	64	60	68	63	60	67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	399803
5°	393223
10°	374678
15°	342374
20°	293610
25°	235582
30°	165176
35°	76317
40°	24498
45°	7908
50°	3676
55°	3246
60°	3236
65°	2948
70°	2910
75°	3347
80°	4288
85°	7147



TEST NUMBER: P366413

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-WMH-BTR86

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	513.1	13.3
10°-20°	1278.1	33.1
20°-30°	1342.3	34.7
30°-40°	595.6	15.4
40°-50°	77.0	2.0
50°-60°	24.0	0.6
60°-70°	17.0	0.4
70°-80°	12.4	0.3
80°-90°	7.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3133.5	81.0
0°-40°	3729.1	96.4
0°-60°	3830.1	99.0
0°-90°	3867.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3867.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5584	
5°	5471	513
15°	4619	1278
25°	2982	1342
35°	873	596
45°	78	77
55°	26	24
65°	17	17
75°	12	12
85°	9	8
90°	0	



TEST NUMBER: P366413

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-WMH-BTR86

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	5583.7
2.5°	5549.0
5°	5470.9
7.5°	5365.0
10°	5153.3
12.5°	4915.5
15°	4618.7
17.5°	4262.9
20°	3853.3
22.5°	3422.8
25°	2981.9
27.5°	2487.3
30°	1997.8
32.5°	1468.4
35°	873.1
37.5°	465.2
40°	262.1
42.5°	144.1
45°	78.1
47.5°	39.9
50°	33.0
52.5°	29.5
55°	26.0
57.5°	24.3
60°	22.6
62.5°	19.1
65°	17.4
67.5°	13.9
70°	13.9
72.5°	12.1
75°	12.1
77.5°	10.4
80°	10.4
82.5°	8.7
85°	8.7
87.5°	5.2
90°	0.0

(END OF REPORT)