

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366414

Luminaire Tested: **FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-WMH-BTR87**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P366414  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-30)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-WMH-BTR87  
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, WARM HAZE REFLECTOR,  
BOTTOM TRIM POLYCARBONATE, CLEAR 0.375", 5000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3937.0 lumens  
Efficiency: N/A  
Efficacy: 71.5 lumens/watt  
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.8  
Luminous Opening: Circular (Dia: 0.44' x H: 0')  
CIE Type: Direct


Input Watts (W): 55.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P366414

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-WMH-BTR87

### Luminous Intensity Polar Plot





TEST NUMBER: P366414

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-WMH-BTR87

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	92	90	88
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	84	83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	80	78
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74
6	90	82	76	72	89	81	76	72	80	75	72	78	74	71	77	74	71	69
7	86	78	72	68	85	77	72	68	76	71	68	75	70	67	73	70	67	66
8	82	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62
9	79	70	64	61	78	69	64	61	69	64	60	68	63	60	67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	407042
5°	400346
10°	381462
15°	348571
20°	298921
25°	239848
30°	168168
35°	77699
40°	24938
45°	8050
50°	3743
55°	3308
60°	3294
65°	2999
70°	2952
75°	3430
80°	4371
85°	7230



TEST NUMBER: P366414

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-WMH-BTR87

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	522.4	13.3
10°-20°	1301.2	33.1
20°-30°	1366.6	34.7
30°-40°	606.4	15.4
40°-50°	78.3	2.0
50°-60°	24.5	0.6
60°-70°	17.2	0.4
70°-80°	12.6	0.3
80°-90°	7.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3190.2	81.0
0°-40°	3796.6	96.4
0°-60°	3899.4	99.0
0°-90°	3937.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3937.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5685	
5°	5570	522
15°	4702	1301
25°	3036	1367
35°	889	606
45°	80	78
55°	26	24
65°	18	17
75°	12	13
85°	9	8
90°	0	



TEST NUMBER: P366414

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-WMH-BTR87

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	5684.8
2.5°	5649.5
5°	5570.0
7.5°	5462.2
10°	5246.6
12.5°	5004.5
15°	4702.3
17.5°	4340.0
20°	3923.0
22.5°	3484.8
25°	3035.9
27.5°	2532.3
30°	2034.0
32.5°	1495.0
35°	888.9
37.5°	473.6
40°	266.8
42.5°	146.7
45°	79.5
47.5°	40.6
50°	33.6
52.5°	30.0
55°	26.5
57.5°	24.7
60°	23.0
62.5°	19.4
65°	17.7
67.5°	14.1
70°	14.1
72.5°	12.4
75°	12.4
77.5°	10.6
80°	10.6
82.5°	8.8
85°	8.8
87.5°	5.3
90°	0.0

(END OF REPORT)