

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364989

Luminaire Tested: **FLD6BX60D010TE-FEU6B67-8027-F6LBXVM1-LI-BTR84**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364989
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-24)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX60D010TE-FEU6B67-8027-F6LBXVM1-LI-BTR84
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM POLYCARBONATE, CLEAR 0.125", 6000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4323.0 lumens
Efficiency: N/A
Efficacy: 74.4 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 58.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364989

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8027-F6LBXVM1-LI-BTR84

Luminous Intensity Polar Plot





TEST NUMBER: P364989

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8027-F6LBXVM1-LI-BTR84

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	87		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	91	82	77	73	89	82	76	73	80	76	72		79	75	72		78	74	71	70
7	87	78	73	69	85	77	72	69	76	72	68		75	71	68		74	70	68	66
8	83	74	69	65	82	74	68	65	73	68	65		72	67	64		71	67	64	63
9	79	71	65	62	78	70	65	61	69	65	61		68	64	61		68	64	61	60
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	485203
5°	474147
10°	437111
15°	387154
20°	327777
25°	259678
30°	182488
35°	76003
40°	26078
45°	6967
50°	3832
55°	3583
60°	3279
65°	3236
70°	3203
75°	3707
80°	4742
85°	7887



TEST NUMBER: P364989

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8027-F6LBXVM1-LI-BTR84

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	611.3	14.1
10°-20°	1448.9	33.5
20°-30°	1487.4	34.4
30°-40°	629.9	14.6
40°-50°	77.4	1.8
50°-60°	25.7	0.6
60°-70°	18.9	0.4
70°-80°	14.7	0.3
80°-90°	8.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3547.7	82.1
0°-40°	4177.5	96.6
0°-60°	4280.6	99.0
0°-90°	4323.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4323.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6776	
5°	6597	611
15°	5223	1449
25°	3287	1487
35°	870	630
45°	69	77
55°	29	26
65°	19	19
75°	13	15
85°	10	9
90°	0	



TEST NUMBER: P364989

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8027-F6LBXVM1-LI-BTR84

CANDELA DISTRIBUTION (FULL):

0°	
0°	6776.4
2.5°	6732.4
5°	6596.8
7.5°	6363.6
10°	6012.0
12.5°	5637.4
15°	5222.8
17.5°	4777.5
20°	4301.7
22.5°	3795.2
25°	3286.9
27.5°	2761.4
30°	2207.2
32.5°	1555.6
35°	869.5
37.5°	498.8
40°	279.0
42.5°	147.1
45°	68.8
47.5°	40.1
50°	34.4
52.5°	30.6
55°	28.7
57.5°	26.8
60°	22.9
62.5°	21.0
65°	19.1
67.5°	17.2
70°	15.3
72.5°	15.3
75°	13.4
77.5°	13.4
80°	11.5
82.5°	11.5
85°	9.6
87.5°	5.7
90°	0.0

(END OF REPORT)