

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364993

Luminaire Tested: **FLD6BX60D010TE-FEU6B67-8027-F6LBXVM1-LI-BTR89BI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364993
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-22)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX60D010TE-FEU6B67-8027-F6LBXVM1-LI-BTR89BI
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM ACRYLIC, CLEAR RFI 0.125", 6000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4190.0 lumens
Efficiency: N/A
Efficacy: 72.1 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 58.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364993

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8027-F6LBXVM1-LI-BTR89BI

Luminous Intensity Polar Plot





TEST NUMBER: P364993

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8027-F6LBXVM1-LI-BTR89BI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	87		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	79
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	91	82	77	73	89	82	76	73	80	76	72		79	75	72		78	74	71	70
7	87	78	73	69	85	77	72	69	76	72	68		75	71	68		74	70	68	66
8	83	74	69	65	82	74	68	65	73	68	65		72	67	64		71	67	64	63
9	79	71	65	62	78	70	65	61	69	65	61		68	64	61		68	64	61	60
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	469493
5°	458586
10°	421494
15°	375116
20°	317734
25°	252662
30°	177643
35°	74132
40°	25601
45°	6622
50°	3342
55°	3083
60°	3036
65°	2999
70°	2952
75°	3901
80°	4371
85°	7230



TEST NUMBER: P364993

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8027-F6LBXVM1-LI-BTR89BI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	590.7	14.1
10°-20°	1401.8	33.5
20°-30°	1446.4	34.5
30°-40°	615.3	14.7
40°-50°	73.8	1.8
50°-60°	22.3	0.5
60°-70°	17.5	0.4
70°-80°	14.0	0.3
80°-90°	8.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3438.9	82.1
0°-40°	4054.2	96.8
0°-60°	4150.3	99.1
0°-90°	4190.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4190.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6557	
5°	6380	591
15°	5060	1402
25°	3198	1446
35°	848	615
45°	65	74
55°	25	22
65°	18	17
75°	14	14
85°	9	8
90°	0	



TEST NUMBER: P364993

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8027-F6LBXVM1-LI-BTR89BI

CANDELA DISTRIBUTION (FULL):

	0°
0°	6557.0
2.5°	6514.6
5°	6380.3
7.5°	6147.1
10°	5797.2
12.5°	5452.7
15°	5060.4
17.5°	4618.7
20°	4169.9
22.5°	3701.7
25°	3198.1
27.5°	2678.6
30°	2148.6
32.5°	1523.1
35°	848.1
37.5°	487.7
40°	273.9
42.5°	141.4
45°	65.4
47.5°	35.3
50°	30.0
52.5°	26.5
55°	24.7
57.5°	23.0
60°	21.2
62.5°	19.4
65°	17.7
67.5°	15.9
70°	14.1
72.5°	14.1
75°	14.1
77.5°	12.4
80°	10.6
82.5°	10.6
85°	8.8
87.5°	5.3
90°	0.0

(END OF REPORT)