

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365039

Luminaire Tested: **FLD6BX60D010TE-FEU6B67-8040-F6LBXVM1-LI-BL89BW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365039
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-42)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX60D010TE-FEU6B67-8040-F6LBXVM1-LI-BL89BW
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, SPECULAR CLEAR REFLECTOR,
BOTTOM LENS ACRYLIC OPAL SMOOTH, CLEAR 0.125", 6000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4246.0 lumens
Efficiency: N/A
Efficacy: 73.1 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.36
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 58.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365039

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8040-F6LBXVM1-LI-BL89BW

Luminous Intensity Polar Plot





TEST NUMBER: P365039

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8040-F6LBXVM1-LI-BL89BW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	109	104	100	96	106	102	98	95	98	94	92		94	91	89		90	88	86	84
2	99	91	84	78	96	89	83	77	85	80	75		82	78	74		79	75	72	70
3	90	80	71	65	88	78	70	64	75	69	63		72	67	62		70	65	61	59
4	83	71	62	55	80	69	61	55	67	59	54		64	58	53		62	57	52	50
5	76	63	54	47	74	62	53	47	60	52	46		58	51	46		56	50	45	43
6	70	57	48	41	68	56	47	41	54	46	41		52	45	40		51	45	40	38
7	65	51	43	36	63	51	42	36	49	41	36		48	41	36		46	40	35	33
8	60	47	38	32	59	46	38	32	45	37	32		44	37	32		42	36	32	30
9	56	43	35	29	55	42	34	29	41	34	29		40	34	29		39	33	29	27
10	53	40	32	26	52	39	32	26	38	31	26		37	31	26		36	30	26	24

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	41396
5°	41384
10°	40950
15°	40702
20°	40582
25°	40151
30°	39877
35°	39481
40°	38913
45°	38498
50°	37889
55°	37165
60°	35996
65°	34469
70°	32233
75°	28685
80°	22998
85°	14197



TEST NUMBER: P365039

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8040-F6LBXVM1-LI-BL89BW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	143.0	3.4
10°-20°	407.0	9.6
20°-30°	615.1	14.5
30°-40°	739.7	17.4
40°-50°	768.3	18.1
50°-60°	696.5	16.4
60°-70°	527.2	12.4
70°-80°	287.9	6.8
80°-90°	61.3	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1165.0	27.4
0°-40°	1904.7	44.9
0°-60°	3369.5	79.4
0°-90°	4246.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4246.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1516	
5°	1509	143
15°	1439	407
25°	1332	615
35°	1184	740
45°	997	768
55°	780	697
65°	533	527
75°	272	288
85°	45	61
90°	0	



TEST NUMBER: P365039

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8040-F6LBXVM1-LI-BL89BW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1515.5
2.5°	1509.3
5°	1509.3
7.5°	1497.0
10°	1476.4
12.5°	1466.1
15°	1439.3
17.5°	1418.7
20°	1396.1
22.5°	1369.3
25°	1332.2
27.5°	1299.3
30°	1264.3
32.5°	1225.2
35°	1184.0
37.5°	1136.6
40°	1091.3
42.5°	1046.0
45°	996.6
47.5°	945.1
50°	891.6
52.5°	838.1
55°	780.4
57.5°	720.7
60°	658.9
62.5°	597.1
65°	533.3
67.5°	469.5
70°	403.6
72.5°	337.7
75°	271.8
77.5°	208.0
80°	146.2
82.5°	92.7
85°	45.3
87.5°	14.4
90°	0.0

(END OF REPORT)