

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365753

Luminaire Tested: **FLD6BX60D010TE-FEU6B67-8040-F6LBXVM1-MW-BL84**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365753
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-36)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX60D010TE-FEU6B67-8040-F6LBXVM1-MW-BL84
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, MATTE WHITE REFLECTOR, BOTTOM LENS POLYCARBONATE, CLEAR 0.125", 6000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4740.0 lumens
Efficiency: N/A
Efficacy: 81.6 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.95
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 58.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365753

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8040-F6LBXVM1-MW-BL84

Luminous Intensity Polar Plot





TEST NUMBER: P365753

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8040-F6LBXVM1-MW-BL84

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97		98	96	95		95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86		90	87	84		87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76		82	78	75		80	77	74	72
4	91	82	75	70	89	80	74	69	78	73	68		76	71	67		74	70	67	65
5	85	75	68	63	84	74	67	62	72	66	62		70	65	61		69	64	61	59
6	80	69	62	57	78	68	62	57	67	61	56		65	60	56		64	59	55	54
7	75	64	57	52	74	64	57	52	62	56	52		61	55	51		60	55	51	49
8	71	60	53	48	70	59	52	48	58	52	47		57	51	47		56	51	47	45
9	67	56	49	44	66	55	49	44	54	48	44		53	48	44		52	47	44	42
10	64	52	46	41	62	52	45	41	51	45	41		50	45	41		49	44	41	39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	105014
5°	102873
10°	97725
15°	91423
20°	85295
25°	78259
30°	66832
35°	50949
40°	37519
45°	28478
50°	23190
55°	20397
60°	18225
65°	16107
70°	13649
75°	10649
80°	7126
85°	3228



TEST NUMBER: P365753

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8040-F6LBXVM1-MW-BL84

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	350.8	7.4
10°-20°	907.2	19.1
20°-30°	1179.1	24.9
30°-40°	960.8	20.3
40°-50°	583.2	12.3
50°-60°	385.9	8.1
60°-70°	247.6	5.2
70°-80°	109.2	2.3
80°-90°	16.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2437.1	51.4
0°-40°	3397.8	71.7
0°-60°	4366.9	92.1
0°-90°	4740.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4740.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3844	
5°	3752	351
15°	3233	907
25°	2597	1179
35°	1528	961
45°	737	583
55°	428	386
65°	249	248
75°	101	109
85°	10	16
90°	0	



TEST NUMBER: P365753

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8040-F6LBXVM1-MW-BL84

CANDELA DISTRIBUTION (FULL):

	0°
0°	3844.5
2.5°	3819.8
5°	3751.8
7.5°	3648.9
10°	3523.3
12.5°	3383.2
15°	3232.9
17.5°	3078.5
20°	2934.3
22.5°	2777.8
25°	2596.6
27.5°	2382.5
30°	2118.9
32.5°	1822.4
35°	1527.9
37.5°	1266.4
40°	1052.2
42.5°	873.1
45°	737.2
47.5°	630.1
50°	545.7
52.5°	481.8
55°	428.3
57.5°	378.9
60°	333.6
62.5°	290.3
65°	249.2
67.5°	210.0
70°	170.9
72.5°	133.8
75°	100.9
77.5°	72.1
80°	45.3
82.5°	24.7
85°	10.3
87.5°	2.1
90°	0.0

(END OF REPORT)