

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365701

Luminaire Tested: **FLD6BX60D010TE-FEU6B67-8027-F6LBXVM1-MW-BL86**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365701
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-38)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX60D010TE-FEU6B67-8027-F6LBXVM1-MW-BL86
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, MATTE WHITE REFLECTOR, BOTTOM LENS POLYCARBONATE, CLEAR 0.250", 6000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4327.9 lumens
Efficiency: N/A
Efficacy: 74.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.95
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 58.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365701

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8027-F6LBXVM1-MW-BL86

Luminous Intensity Polar Plot





TEST NUMBER: P365701

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8027-F6LBXVM1-MW-BL86

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97		98	96	95		95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86		90	87	84		87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76		83	78	75		80	77	74	72
4	91	82	75	70	89	80	74	69	78	73	68		76	71	67		74	70	67	65
5	85	75	68	63	84	74	67	62	72	66	62		70	65	61		69	64	61	59
6	80	69	62	57	78	68	62	57	67	61	56		65	60	56		64	59	55	54
7	75	64	57	52	74	64	57	52	62	56	52		61	55	51		60	55	51	49
8	71	60	53	48	70	59	52	48	58	52	47		57	51	47		56	51	47	45
9	67	56	49	44	66	55	49	44	54	48	44		53	48	44		52	47	44	42
10	64	52	46	41	62	52	45	41	51	45	41		50	45	41		49	44	41	39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	96057
5°	93802
10°	88954
15°	83293
20°	77790
25°	71616
30°	61212
35°	46561
40°	34124
45°	25975
50°	21184
55°	18649
60°	16591
65°	14568
70°	12355
75°	9678
80°	6607
85°	3009



TEST NUMBER: P365701

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8027-F6LBXVM1-MW-BL86

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	319.7	7.4
10°-20°	827.9	19.1
20°-30°	1077.9	24.9
30°-40°	879.7	20.3
40°-50°	531.8	12.3
50°-60°	352.2	8.1
60°-70°	224.2	5.2
70°-80°	99.3	2.3
80°-90°	15.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2225.6	51.4
0°-40°	3105.3	71.8
0°-60°	3989.4	92.2
0°-90°	4327.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4327.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3517	
5°	3421	320
15°	2945	828
25°	2376	1078
35°	1396	880
45°	672	532
55°	392	352
65°	225	224
75°	92	99
85°	10	15
90°	0	



TEST NUMBER: P365701

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8027-F6LBXVM1-MW-BL86

CANDELA DISTRIBUTION (FULL):

	0°
0°	3516.6
2.5°	3480.3
5°	3421.0
7.5°	3327.4
10°	3207.1
12.5°	3084.9
15°	2945.4
17.5°	2819.4
20°	2676.1
22.5°	2538.6
25°	2376.2
27.5°	2177.5
30°	1940.7
32.5°	1675.2
35°	1396.3
37.5°	1159.4
40°	957.0
42.5°	796.5
45°	672.4
47.5°	574.9
50°	498.5
52.5°	439.3
55°	391.6
57.5°	345.7
60°	303.7
62.5°	263.6
65°	225.4
67.5°	189.1
70°	154.7
72.5°	122.2
75°	91.7
77.5°	64.9
80°	42.0
82.5°	22.9
85°	9.6
87.5°	1.9
90°	0.0

(END OF REPORT)