

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365707

Luminaire Tested: **FLD6BX60D010TE-FEU6B67-8027-F6LBXVM1-MW-BTR81**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365707
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-19)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX60D010TE-FEU6B67-8027-F6LBXVM1-MW-BTR81
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, MATTE WHITE REFLECTOR,
BOTTOM TRIM POLYCARBONATE, PATTERN 12 0.156", 6000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3008.0 lumens
Efficiency: N/A
Efficacy: 51.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.19
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 58.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365707

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8027-F6LBXVM1-MW-BTR81

Luminous Intensity Polar Plot





TEST NUMBER: P365707

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8027-F6LBXVM1-MW-BTR81

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	107	103	100	108	105	101	99	101	98	96		97	95	93		93	91	90	88
2	103	96	90	85	100	94	89	84	90	86	82		87	84	80		84	81	79	77
3	95	86	79	73	93	84	78	73	81	76	71		79	74	70		76	72	69	67
4	88	77	70	64	86	76	69	64	74	68	63		72	66	62		70	65	61	59
5	82	70	62	57	80	69	62	56	67	61	56		65	60	55		64	59	55	53
6	76	64	56	51	74	63	56	50	62	55	50		60	54	49		58	53	49	47
7	71	59	51	45	69	58	51	45	57	50	45		55	49	45		54	49	44	43
8	66	54	46	41	65	54	46	41	52	46	41		51	45	41		50	45	40	39
9	62	50	43	38	61	50	42	37	48	42	37		47	41	37		46	41	37	35
10	59	47	39	34	58	46	39	34	45	39	34		44	38	34		43	38	34	32

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	108921
5°	111256
10°	114069
15°	113467
20°	110524
25°	105383
30°	97958
35°	89202
40°	79487
45°	68695
50°	57267
55°	47474
60°	39682
65°	33665
70°	28807
75°	23792
80°	18926
85°	14130



TEST NUMBER: P365707

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8027-F6LBXVM1-MW-BTR81

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.5	4.9
10°-20°	430.0	14.3
20°-30°	611.5	20.3
30°-40°	635.9	21.1
40°-50°	522.6	17.4
50°-60°	345.1	11.5
60°-70°	200.0	6.6
70°-80°	93.2	3.1
80°-90°	21.3	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1190.0	39.6
0°-40°	1825.9	60.7
0°-60°	2693.6	89.5
0°-90°	3008.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3008.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1521	
5°	1548	149
15°	1531	430
25°	1334	612
35°	1020	636
45°	678	523
55°	380	345
65°	199	200
75°	86	93
85°	17	21
90°	0	



TEST NUMBER: P365707

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8027-F6LBXVM1-MW-BTR81

CANDELA DISTRIBUTION (FULL):

0°	
0°	1521.2
2.5°	1530.7
5°	1547.9
7.5°	1565.1
10°	1568.9
12.5°	1551.7
15°	1530.7
17.5°	1498.2
20°	1450.5
22.5°	1396.9
25°	1333.9
27.5°	1267.0
30°	1184.8
32.5°	1104.6
35°	1020.5
37.5°	932.6
40°	850.4
42.5°	762.5
45°	678.4
47.5°	594.3
50°	514.1
52.5°	447.2
55°	380.3
57.5°	324.9
60°	277.1
62.5°	235.1
65°	198.7
67.5°	168.2
70°	137.6
72.5°	110.8
75°	86.0
77.5°	65.0
80°	45.9
82.5°	30.6
85°	17.2
87.5°	7.6
90°	0.0

(END OF REPORT)