

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365056

Luminaire Tested: **FLD6BX60D010TE-FEU6B67-8050-F6LBXVM1-LI-BL89BV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365056
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-41)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX60D010TE-FEU6B67-8050-F6LBXVM1-LI-BL89BV
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, SPECULAR CLEAR REFLECTOR,
BOTTOM LENS ACRYLIC, CLEAR 0.125", 6000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5879.9 lumens
Efficiency: N/A
Efficacy: 101.2 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.82
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 58.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365056

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8050-F6LBXVM1-LI-BL89BV

Luminous Intensity Polar Plot





TEST NUMBER: P365056

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8050-F6LBXVM1-LI-BL89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	91	90	88
3	103	97	93	89	101	96	92	88	93	90	87		91	88	85		89	86	84	83
4	99	91	86	82	97	90	85	82	88	84	81		86	83	80		84	81	79	77
5	94	86	81	76	92	85	80	76	83	79	75		82	78	75		80	77	74	73
6	90	81	75	71	88	80	75	71	79	74	71		77	73	70		76	73	70	68
7	85	77	71	67	84	76	71	67	75	70	66		74	69	66		72	69	66	64
8	82	73	67	63	80	72	67	63	71	66	63		70	65	62		69	65	62	61
9	78	69	63	59	77	68	63	59	67	62	59		66	62	59		66	62	59	57
10	74	65	60	56	74	65	60	56	64	59	56		63	59	56		63	59	56	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	227654
5°	223031
10°	205897
15°	183026
20°	156196
25°	130870
30°	102568
35°	54077
40°	25267
45°	9939
50°	2601
55°	705
60°	459
65°	407
70°	335
75°	443
80°	330
85°	658



TEST NUMBER: P365056

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8050-F6LBXVM1-LI-BL89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	752.8	12.8
10°-20°	1797.4	30.6
20°-30°	1977.0	33.6
30°-40°	1091.3	18.6
40°-50°	230.3	3.9
50°-60°	18.8	0.3
60°-70°	5.7	0.1
70°-80°	4.7	0.1
80°-90°	2.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4527.2	77.0
0°-40°	5618.5	95.6
0°-60°	5867.5	99.8
0°-90°	5879.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5879.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8334	
5°	8134	753
15°	6472	1797
25°	4342	1977
35°	1622	1091
45°	257	230
55°	15	19
65°	6	6
75°	4	5
85°	2	2
90°	0	



TEST NUMBER: P365056

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8050-F6LBXVM1-LI-BL89BV

CANDELA DISTRIBUTION (FULL):

0°	
0°	8334.3
2.5°	8271.0
5°	8134.0
7.5°	7824.0
10°	7423.3
12.5°	6963.5
15°	6472.2
17.5°	5944.9
20°	5373.4
22.5°	4854.7
25°	4342.2
27.5°	3821.3
30°	3251.9
32.5°	2475.8
35°	1621.7
37.5°	1077.6
40°	708.6
42.5°	447.1
45°	257.3
47.5°	135.0
50°	61.2
52.5°	25.3
55°	14.8
57.5°	10.5
60°	8.4
62.5°	6.3
65°	6.3
67.5°	4.2
70°	4.2
72.5°	6.3
75°	4.2
77.5°	4.2
80°	2.1
82.5°	2.1
85°	2.1
87.5°	2.1
90°	0.0

(END OF REPORT)