

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P236161

Luminaire Tested: **FLD6BX70D010 EU6B6/78040 F6LBXVM1LIBL84**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P236161
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX70D010 EU6B6/78040 F6LBXVM1LIBL84
Description: FAILSAFE 6 INCH RECESSED LED DOWNLIGHT
6" LED Vandal Resistant, Medium (50° Beam), Specular Clear, Bottom lens,
0.125" clear polycarbonate
Light Source: (1) 4000K CCT, 80 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5649.3 lumens
Efficiency: N/A
Efficacy: 71.1 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 79.45
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P236161

CATALOG NUMBER: FLD6BX70D010 EU6B6/78040 F6LBXVM1LIBL84

Luminous Intensity Polar Plot





TEST NUMBER: P236161

CATALOG NUMBER: FLD6BX70D010 EU6B6/78040 F6LBXVM1LIBL84

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79
4	96	88	82	78	94	87	82	77	85	80	77	83	79	76	81	78	75	73
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	64	63
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51
10	70	60	54	50	69	59	54	50	59	53	50	58	53	49	57	53	49	48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	384065
5°	378806
10°	361272
15°	337508
20°	315250
25°	285795
30°	233775
35°	159917
40°	95224
45°	51576
50°	25476
55°	15571
60°	10425
65°	7039
70°	4349
75°	2874
80°	4283
85°	0



TEST NUMBER: P236161

CATALOG NUMBER: FLD6BX70D010 EU6B6/78040 F6LBXVM1LIBL84

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	540.8	9.6
10°-20°	1403.3	24.8
20°-30°	1788.0	31.6
30°-40°	1263.6	22.4
40°-50°	461.3	8.2
50°-60°	127.9	2.3
60°-70°	46.4	0.8
70°-80°	16.5	0.3
80°-90°	1.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3732.1	66.1
0°-40°	4995.7	88.4
0°-60°	5584.9	98.9
0°-90°	5649.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5649.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5887	
5°	5784	541
15°	4997	1403
25°	3970	1788
35°	2008	1264
45°	559	461
55°	137	128
65°	46	46
75°	11	17
85°	0	2
90°	0	



TEST NUMBER: P236161

CATALOG NUMBER: FLD6BX70D010 EU6B6/78040 F6LBXVM1LIBL84

CANDELA DISTRIBUTION (FULL):

	0°
0°	5886.9
2.5°	5864.1
5°	5784.2
7.5°	5624.5
10°	5453.4
12.5°	5225.2
15°	4997.0
17.5°	4768.9
20°	4540.7
22.5°	4266.9
25°	3970.2
27.5°	3559.5
30°	3103.2
32.5°	2555.6
35°	2007.9
37.5°	1528.8
40°	1118.1
42.5°	810.0
45°	559.0
47.5°	376.5
50°	251.0
52.5°	171.1
55°	136.9
57.5°	102.7
60°	79.9
62.5°	57.0
65°	45.6
67.5°	34.2
70°	22.8
72.5°	22.8
75°	11.4
77.5°	11.4
80°	11.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)