

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365013

Luminaire Tested: **FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-LI-BTR94**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365013
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-27)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-LI-BTR94
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM GLASS, TEMPERED CLEAR 0.187", 6000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4616.1 lumens
Efficiency: N/A
Efficacy: 79.5 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 58.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365013

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-LI-BTR94

Luminous Intensity Polar Plot





TEST NUMBER: P365013

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-LI-BTR94

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94	92	90	88
3	104	98	93	90	102	96	92	89	94	90	87		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	91	82	77	73	89	82	76	73	80	76	72		79	75	72		77	74	71	70
7	87	78	73	69	85	77	72	68	76	72	68		75	71	68		74	70	67	66
8	83	74	69	65	82	74	68	65	73	68	64		72	67	64		71	67	64	63
9	79	71	65	61	78	70	65	61	69	64	61		68	64	61		67	64	61	59
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	516672
5°	502998
10°	464943
15°	413907
20°	348594
25°	277786
30°	194576
35°	82419
40°	28761
45°	7888
50°	4010
55°	3745
60°	3723
65°	3388
70°	3350
75°	4426
80°	5773
85°	8215



TEST NUMBER: P365013

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-LI-BTR94

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	648.9	14.1
10°-20°	1543.7	33.4
20°-30°	1587.9	34.4
30°-40°	678.2	14.7
40°-50°	84.7	1.8
50°-60°	27.1	0.6
60°-70°	20.0	0.4
70°-80°	16.1	0.3
80°-90°	9.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3780.5	81.9
0°-40°	4458.7	96.6
0°-60°	4570.4	99.0
0°-90°	4616.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4616.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7216	
5°	6998	649
15°	5584	1544
25°	3516	1588
35°	943	678
45°	78	85
55°	30	27
65°	20	20
75°	16	16
85°	10	10
90°	0	



TEST NUMBER: P365013

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-LI-BTR94

CANDELA DISTRIBUTION (FULL):

0°	
0°	7215.9
2.5°	7158.0
5°	6998.2
7.5°	6742.5
10°	6394.8
12.5°	6007.3
15°	5583.7
17.5°	5080.3
20°	4574.9
22.5°	4055.5
25°	3516.1
27.5°	2946.7
30°	2353.4
32.5°	1672.1
35°	942.9
37.5°	539.4
40°	307.7
42.5°	159.8
45°	77.9
47.5°	42.0
50°	36.0
52.5°	32.0
55°	30.0
57.5°	28.0
60°	26.0
62.5°	22.0
65°	20.0
67.5°	18.0
70°	16.0
72.5°	16.0
75°	16.0
77.5°	14.0
80°	14.0
82.5°	12.0
85°	10.0
87.5°	6.0
90°	0.0

(END OF REPORT)