

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365721

Luminaire Tested: **FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-MW-BL89AM**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P365721  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-40)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-MW-BL89AM  
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, MATTE WHITE REFLECTOR, BOTTOM LENS POLYCARBONATE, OPAL SMOOTH 0.125", 6000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2027.0 lumens  
Efficiency: N/A  
Efficacy: 34.9 lumens/watt  
Spacing Criteria (0/90/45): 1.25 / 1.25 / 1.37  
Luminous Opening: Circular (Dia: 0.71' x H: 0')  
CIE Type: Direct


Input Watts (W): 58.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P365721

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-MW-BL89AM

### Luminous Intensity Polar Plot





TEST NUMBER: P365721

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-MW-BL89AM

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	104	100	96	106	102	98	95	98	94	92	94	91	89	90	88	86	84
2	99	91	84	78	96	89	83	77	85	80	75	82	78	74	79	75	72	70
3	90	80	71	65	88	78	70	64	75	69	63	72	67	62	70	65	61	59
4	82	70	62	55	80	69	61	55	67	59	54	64	58	53	62	57	52	50
5	76	63	54	47	74	62	53	47	60	52	46	58	51	46	56	50	45	43
6	70	57	48	41	68	56	47	41	54	46	41	52	45	40	51	45	40	38
7	65	51	42	36	63	50	42	36	49	41	36	47	41	36	46	40	35	33
8	60	47	38	32	59	46	38	32	45	37	32	43	37	32	42	36	32	30
9	56	43	35	29	55	42	34	29	41	34	29	40	33	29	39	33	29	27
10	53	40	32	26	52	39	31	26	38	31	26	37	31	26	36	30	26	24

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	19481
5°	19556
10°	19449
15°	19377
20°	19278
25°	19087
30°	18966
35°	18850
40°	18592
45°	18365
50°	18167
55°	17887
60°	17241
65°	16527
70°	15478
75°	13699
80°	10995
85°	6268



TEST NUMBER: P365721

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-MW-BL89AM

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	67.6	3.3
10°-20°	193.2	9.5
20°-30°	292.4	14.4
30°-40°	352.9	17.4
40°-50°	367.4	18.1
50°-60°	334.2	16.5
60°-70°	252.8	12.5
70°-80°	137.9	6.8
80°-90°	28.5	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	553.2	27.3
0°-40°	906.1	44.7
0°-60°	1607.7	79.3
0°-90°	2027.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2027.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	713	
5°	713	68
15°	685	193
25°	633	292
35°	565	353
45°	475	367
55°	376	334
65°	256	253
75°	130	138
85°	20	29
90°	0	



TEST NUMBER: P365721

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-MW-BL89AM

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	713.2
2.5°	715.2
5°	713.2
7.5°	707.2
10°	701.2
12.5°	693.2
15°	685.2
17.5°	673.2
20°	663.2
22.5°	649.2
25°	633.3
27.5°	619.3
30°	601.3
32.5°	583.3
35°	565.3
37.5°	543.4
40°	521.4
42.5°	499.4
45°	475.4
47.5°	453.5
50°	427.5
52.5°	401.5
55°	375.6
57.5°	345.6
60°	315.6
62.5°	285.7
65°	255.7
67.5°	225.7
70°	193.8
72.5°	161.8
75°	129.8
77.5°	99.9
80°	69.9
82.5°	43.9
85°	20.0
87.5°	6.0
90°	0.0

(END OF REPORT)