

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365090

Luminaire Tested: **FLD6BX70D010TE-FEU6B67-8030-F6LBXVM1-LI-BL87**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365090
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-43)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX70D010TE-FEU6B67-8030-F6LBXVM1-LI-BL87
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, SPECULAR CLEAR REFLECTOR,
BOTTOM LENS POLYCARBONATE, CLEAR 0.375", 7000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5875.9 lumens
Efficiency: N/A
Efficacy: 80.1 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.82
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 73.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365090

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8030-F6LBXVM1-LI-BL87

Luminous Intensity Polar Plot





TEST NUMBER: P365090

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8030-F6LBXVM1-LI-BL87

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	91	90	88
3	103	97	93	89	101	96	92	88	93	90	87		91	88	85		89	86	84	83
4	99	91	86	82	97	90	85	82	88	84	81		86	83	80		84	81	79	77
5	94	86	80	76	92	85	80	76	83	79	75		82	78	75		80	77	74	73
6	90	81	75	71	88	80	75	71	79	74	71		77	73	70		76	73	70	68
7	85	77	71	67	84	76	71	67	75	70	66		74	69	66		72	69	66	64
8	82	72	67	63	80	72	67	63	71	66	63		70	65	62		69	65	62	61
9	78	69	63	59	77	68	63	59	67	62	59		66	62	59		66	62	59	57
10	74	65	60	56	74	65	60	56	64	59	56		63	59	56		63	58	56	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	226075
5°	221775
10°	204805
15°	182503
20°	155861
25°	130897
30°	102757
35°	53247
40°	25427
45°	10009
50°	2635
55°	738
60°	486
65°	427
70°	351
75°	464
80°	346
85°	689



TEST NUMBER: P365090

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8030-F6LBXVM1-LI-BL87

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	750.0	12.8
10°-20°	1793.6	30.5
20°-30°	1980.3	33.7
30°-40°	1089.7	18.5
40°-50°	230.3	3.9
50°-60°	19.5	0.3
60°-70°	6.0	0.1
70°-80°	4.3	0.1
80°-90°	2.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4524.0	77.0
0°-40°	5613.7	95.5
0°-60°	5863.5	99.8
0°-90°	5875.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5875.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8276	
5°	8088	750
15°	6454	1794
25°	4343	1980
35°	1597	1090
45°	259	230
55°	16	19
65°	7	6
75°	4	4
85°	2	2
90°	0	



TEST NUMBER: P365090

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8030-F6LBXVM1-LI-BL87

CANDELA DISTRIBUTION (FULL):

0°	
0°	8276.5
2.5°	8272.0
5°	8088.2
7.5°	7804.7
10°	7383.9
12.5°	6965.3
15°	6453.7
17.5°	5933.3
20°	5361.9
22.5°	4861.3
25°	4343.1
27.5°	3842.6
30°	3257.9
32.5°	2487.1
35°	1596.8
37.5°	1076.4
40°	713.1
42.5°	445.2
45°	259.1
47.5°	132.9
50°	62.0
52.5°	26.6
55°	15.5
57.5°	11.1
60°	8.9
62.5°	6.6
65°	6.6
67.5°	4.4
70°	4.4
72.5°	6.6
75°	4.4
77.5°	2.2
80°	2.2
82.5°	2.2
85°	2.2
87.5°	2.2
90°	0.0

(END OF REPORT)