

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365807

Luminaire Tested: **FLD6BX70D010TE-FEU6B67-8030-F6LBXVM1-MW-BL84**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P365807  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-36)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX70D010TE-FEU6B67-8030-F6LBXVM1-MW-BL84  
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, MATTE WHITE REFLECTOR, BOTTOM LENS POLYCARBONATE, CLEAR 0.125", 7000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5400.9 lumens  
Efficiency: N/A  
Efficacy: 73.6 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.95  
Luminous Opening: Circular (Dia: 0.71' x H: 0')  
CIE Type: Direct


Input Watts (W): 73.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P365807

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8030-F6LBXVM1-MW-BL84

### Luminous Intensity Polar Plot





TEST NUMBER: P365807

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8030-F6LBXVM1-MW-BL84

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97		98	96	95		95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86		90	87	84		87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76		82	78	75		80	77	74	72
4	91	82	75	70	89	80	74	69	78	73	68		76	71	67		74	70	67	65
5	85	75	68	63	84	74	67	62	72	66	62		70	65	61		69	64	61	59
6	80	69	62	57	78	68	62	57	67	61	56		65	60	56		64	59	55	54
7	75	64	57	52	74	64	57	52	62	56	52		61	55	51		60	55	51	49
8	71	60	53	48	70	59	52	48	58	52	47		57	51	47		56	51	47	45
9	67	56	49	44	66	55	49	44	54	48	44		53	48	44		52	47	44	42
10	64	52	46	41	62	52	45	41	51	45	41		50	45	41		49	44	41	39

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	119657
5°	117219
10°	111352
15°	104171
20°	97190
25°	89172
30°	76152
35°	58055
40°	42753
45°	32449
50°	26423
55°	23240
60°	20765
65°	18349
70°	15550
75°	12137
80°	8117
85°	3667



TEST NUMBER: P365807

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8030-F6LBXVM1-MW-BL84

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	399.7	7.4
10°-20°	1033.7	19.1
20°-30°	1343.5	24.9
30°-40°	1094.8	20.3
40°-50°	664.5	12.3
50°-60°	439.7	8.1
60°-70°	282.1	5.2
70°-80°	124.5	2.3
80°-90°	18.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2776.9	51.4
0°-40°	3871.7	71.7
0°-60°	4975.9	92.1
0°-90°	5400.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5400.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4381	
5°	4275	400
15°	3684	1034
25°	2959	1343
35°	1741	1095
45°	840	665
55°	488	440
65°	284	282
75°	115	124
85°	12	18
90°	0	



TEST NUMBER: P365807

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8030-F6LBXVM1-MW-BL84

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4380.6
2.5°	4352.5
5°	4275.0
7.5°	4157.7
10°	4014.6
12.5°	3855.0
15°	3683.7
17.5°	3507.8
20°	3343.5
22.5°	3165.2
25°	2958.7
27.5°	2714.7
30°	2414.4
32.5°	2076.5
35°	1741.0
37.5°	1443.0
40°	1199.0
42.5°	994.8
45°	840.0
47.5°	718.0
50°	621.8
52.5°	549.0
55°	488.0
57.5°	431.7
60°	380.1
62.5°	330.8
65°	283.9
67.5°	239.3
70°	194.7
72.5°	152.5
75°	115.0
77.5°	82.1
80°	51.6
82.5°	28.2
85°	11.7
87.5°	2.3
90°	0.0

(END OF REPORT)