

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366447

Luminaire Tested: **FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-WMH-BTR84**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P366447  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-30)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-WMH-BTR84  
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, WARM HAZE REFLECTOR,  
BOTTOM TRIM POLYCARBONATE, CLEAR 0.125", 6000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4448.1 lumens  
Efficiency: N/A  
Efficacy: 76.6 lumens/watt  
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.8  
Luminous Opening: Circular (Dia: 0.44' x H: 0')  
CIE Type: Direct


Input Watts (W): 58.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P366447

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-WMH-BTR84

### Luminous Intensity Polar Plot





TEST NUMBER: P366447

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-WMH-BTR84

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	92	90	88
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	84	83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	80	78
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74
6	90	82	76	72	89	81	76	72	80	75	72	78	74	71	77	74	71	69
7	86	78	72	68	85	77	72	68	76	71	68	75	70	67	73	70	67	66
8	82	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62
9	79	70	64	61	78	69	64	61	69	64	60	68	63	60	67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	459877
5°	452304
10°	430975
15°	393811
20°	337721
25°	270983
30°	189987
35°	87777
40°	28181
45°	9093
50°	4222
55°	3733
60°	3723
65°	3388
70°	3350
75°	3873
80°	4948
85°	8215



TEST NUMBER: P366447

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-WMH-BTR84

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	590.2	13.3
10°-20°	1470.1	33.1
20°-30°	1544.0	34.7
30°-40°	685.1	15.4
40°-50°	88.5	2.0
50°-60°	27.7	0.6
60°-70°	19.5	0.4
70°-80°	14.3	0.3
80°-90°	8.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3604.3	81.0
0°-40°	4289.4	96.4
0°-60°	4405.5	99.0
0°-90°	4448.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4448.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6423	
5°	6293	590
15°	5313	1470
25°	3430	1544
35°	1004	685
45°	90	89
55°	30	28
65°	20	20
75°	14	14
85°	10	9
90°	0	



TEST NUMBER: P366447

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-WMH-BTR84

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	6422.7
2.5°	6382.7
5°	6292.9
7.5°	6171.1
10°	5927.6
12.5°	5654.0
15°	5312.6
17.5°	4903.4
20°	4432.2
22.5°	3937.1
25°	3430.0
27.5°	2861.0
30°	2297.9
32.5°	1689.0
35°	1004.2
37.5°	535.1
40°	301.5
42.5°	165.7
45°	89.8
47.5°	45.9
50°	37.9
52.5°	33.9
55°	29.9
57.5°	28.0
60°	26.0
62.5°	22.0
65°	20.0
67.5°	16.0
70°	16.0
72.5°	14.0
75°	14.0
77.5°	12.0
80°	12.0
82.5°	10.0
85°	10.0
87.5°	6.0
90°	0.0

(END OF REPORT)