

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366537

Luminaire Tested: **FLD6BX70D010TE-FEU6B67-8030-F6LBXVM1-WMH-BTR84**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P366537
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-30)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX70D010TE-FEU6B67-8030-F6LBXVM1-WMH-BTR84
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, WARM HAZE REFLECTOR,
BOTTOM TRIM POLYCARBONATE, CLEAR 0.125", 7000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5225.0 lumens
Efficiency: N/A
Efficacy: 71.2 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.8
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 73.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P366537

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8030-F6LBXVM1-WMH-BTR84

Luminous Intensity Polar Plot





TEST NUMBER: P366537

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8030-F6LBXVM1-WMH-BTR84

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	92	90	88
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	84	83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	80	78
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74
6	90	82	76	72	89	81	76	72	80	75	72	78	74	71	77	74	71	69
7	86	78	72	68	85	77	72	68	76	71	68	75	70	67	73	70	67	66
8	82	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62
9	79	70	64	61	78	69	64	61	69	64	60	68	63	60	67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	540207
5°	531317
10°	506255
15°	462609
20°	396713
25°	318315
30°	223183
35°	103117
40°	33098
45°	10683
50°	4968
55°	4394
60°	4368
65°	3981
70°	3936
75°	4537
80°	5814
85°	9612



TEST NUMBER: P366537

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8030-F6LBXVM1-WMH-BTR84

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	693.3	13.3
10°-20°	1726.9	33.1
20°-30°	1813.6	34.7
30°-40°	804.8	15.4
40°-50°	104.0	2.0
50°-60°	32.5	0.6
60°-70°	22.9	0.4
70°-80°	16.7	0.3
80°-90°	10.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4233.9	81.0
0°-40°	5038.7	96.4
0°-60°	5175.1	99.0
0°-90°	5225.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5225.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7545	
5°	7392	693
15°	6241	1727
25°	4029	1814
35°	1180	805
45°	106	104
55°	35	33
65°	24	23
75°	16	17
85°	12	10
90°	0	



TEST NUMBER: P366537

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8030-F6LBXVM1-WMH-BTR84

CANDELA DISTRIBUTION (FULL):

0°	
0°	7544.6
2.5°	7497.7
5°	7392.2
7.5°	7249.1
10°	6963.0
12.5°	6641.7
15°	6240.7
17.5°	5759.9
20°	5206.4
22.5°	4624.8
25°	4029.1
27.5°	3360.7
30°	2699.4
32.5°	1984.1
35°	1179.7
37.5°	628.5
40°	354.1
42.5°	194.7
45°	105.5
47.5°	53.9
50°	44.6
52.5°	39.9
55°	35.2
57.5°	32.8
60°	30.5
62.5°	25.8
65°	23.5
67.5°	18.8
70°	18.8
72.5°	16.4
75°	16.4
77.5°	14.1
80°	14.1
82.5°	11.7
85°	11.7
87.5°	7.0
90°	0.0

(END OF REPORT)