

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365742

Luminaire Tested: **FLD6BX60D010TE-FEU6B67-8035-F6LBXVM1-MW-BTR80**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365742
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-14)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX60D010TE-FEU6B67-8035-F6LBXVM1-MW-BTR80
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, MATTE WHITE REFLECTOR,
BOTTOM TRIM ACRYLIC, PATTERN 12 0.125", 6000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3533.0 lumens
Efficiency: N/A
Efficacy: 60.8 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.95
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 58.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365742

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8035-F6LBXVM1-MW-BTR80

Luminous Intensity Polar Plot





TEST NUMBER: P365742

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8035-F6LBXVM1-MW-BTR80

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89
2	103	97	91	87	101	95	90	86	92	88	84	89	85	82	86	83	80	78
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70
4	90	80	73	67	88	79	72	67	76	70	66	74	69	65	72	68	64	62
5	84	73	66	60	82	72	65	60	70	64	59	68	63	59	66	62	58	56
6	78	67	60	54	77	66	59	54	65	58	54	63	57	53	62	57	53	51
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	47
8	69	58	50	45	68	57	50	45	56	49	45	55	49	45	53	48	44	43
9	65	54	46	42	64	53	46	42	52	46	41	51	45	41	50	45	41	39
10	62	50	43	39	61	50	43	39	49	43	38	48	42	38	47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	191499
5°	188716
10°	180232
15°	166847
20°	150863
25°	133564
30°	115362
35°	96675
40°	79963
45°	66001
50°	55139
55°	47300
60°	41128
65°	36240
70°	31549
75°	26475
80°	21854
85°	16759



TEST NUMBER: P365742

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8035-F6LBXVM1-MW-BTR80

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	246.0	7.0
10°-20°	628.8	17.8
20°-30°	773.5	21.9
30°-40°	693.5	19.6
40°-50°	507.5	14.4
50°-60°	343.2	9.7
60°-70°	213.2	6.0
70°-80°	103.0	2.9
80°-90°	24.4	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1648.2	46.7
0°-40°	2341.7	66.3
0°-60°	3192.3	90.4
0°-90°	3533.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3533.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2674	
5°	2626	246
15°	2251	629
25°	1691	773
35°	1106	693
45°	652	508
55°	379	343
65°	214	213
75°	96	103
85°	20	24
90°	0	



TEST NUMBER: P365742

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8035-F6LBXVM1-MW-BTR80

CANDELA DISTRIBUTION (FULL):

	0°
0°	2674.5
2.5°	2662.3
5°	2625.6
7.5°	2564.5
10°	2478.9
12.5°	2377.1
15°	2250.8
17.5°	2118.4
20°	1979.9
22.5°	1837.3
25°	1690.6
27.5°	1537.9
30°	1395.3
32.5°	1248.6
35°	1106.0
37.5°	977.7
40°	855.5
42.5°	745.5
45°	651.8
47.5°	568.3
50°	495.0
52.5°	435.9
55°	378.9
57.5°	332.0
60°	287.2
62.5°	248.5
65°	213.9
67.5°	181.3
70°	150.7
72.5°	122.2
75°	95.7
77.5°	71.3
80°	53.0
82.5°	34.6
85°	20.4
87.5°	8.1
90°	0.0

(END OF REPORT)