

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366538

Luminaire Tested: **FLD6BX70D010TE-FEU6B67-8030-F6LBXVM1-WMH-BTR85**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P366538
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-30)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX70D010TE-FEU6B67-8030-F6LBXVM1-WMH-BTR85
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, WARM HAZE REFLECTOR,
BOTTOM TRIM POLYCARBONATE, CLEAR 0.187", 7000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5187.0 lumens
Efficiency: N/A
Efficacy: 70.7 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.8
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 73.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P366538

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8030-F6LBXVM1-WMH-BTR85

Luminous Intensity Polar Plot





TEST NUMBER: P366538

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8030-F6LBXVM1-WMH-BTR85

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	92	90	88
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	84	83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	80	78
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74
6	90	82	76	72	89	81	76	72	80	75	72	78	74	71	77	74	71	69
7	86	78	72	68	85	77	72	68	76	71	68	75	70	67	73	70	67	66
8	82	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62
9	79	70	64	61	78	69	64	61	69	64	60	68	63	60	67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	536284
5°	527450
10°	502576
15°	459243
20°	393832
25°	316000
30°	221554
35°	102366
40°	32864
45°	10612
50°	4924
55°	4357
60°	4339
65°	3948
70°	3894
75°	4509
80°	5773
85°	9530



TEST NUMBER: P366538

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8030-F6LBXVM1-WMH-BTR85

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	688.2	13.3
10°-20°	1714.4	33.1
20°-30°	1800.5	34.7
30°-40°	799.0	15.4
40°-50°	103.2	2.0
50°-60°	32.3	0.6
60°-70°	22.7	0.4
70°-80°	16.6	0.3
80°-90°	10.1	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4203.1	81.0
0°-40°	5002.0	96.4
0°-60°	5137.5	99.0
0°-90°	5187.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5187.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7490	
5°	7338	688
15°	6195	1714
25°	4000	1800
35°	1171	799
45°	105	103
55°	35	32
65°	23	23
75°	16	17
85°	12	10
90°	0	



TEST NUMBER: P366538

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8030-F6LBXVM1-WMH-BTR85

CANDELA DISTRIBUTION (FULL):

	0°
0°	7489.8
2.5°	7443.2
5°	7338.4
7.5°	7196.4
10°	6912.4
12.5°	6593.4
15°	6195.3
17.5°	5718.0
20°	5168.6
22.5°	4591.2
25°	3999.8
27.5°	3336.3
30°	2679.7
32.5°	1969.6
35°	1171.1
37.5°	624.0
40°	351.6
42.5°	193.2
45°	104.8
47.5°	53.5
50°	44.2
52.5°	39.6
55°	34.9
57.5°	32.6
60°	30.3
62.5°	25.6
65°	23.3
67.5°	18.6
70°	18.6
72.5°	16.3
75°	16.3
77.5°	14.0
80°	14.0
82.5°	11.6
85°	11.6
87.5°	7.0
90°	0.0

(END OF REPORT)