

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366458

Luminaire Tested: **FLD6BX60D010TE-FEU6B67-8035-F6LBXVM1-WMH-BL87**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P366458
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-47)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX60D010TE-FEU6B67-8035-F6LBXVM1-WMH-BL87
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, WARM HAZE REFLECTOR, BOTTOM LENS POLYCARBONATE, CLEAR 0.375", 6000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5042.0 lumens
Efficiency: N/A
Efficacy: 86.8 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 58.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P366458

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8035-F6LBXVM1-WMH-BL87

Luminous Intensity Polar Plot





TEST NUMBER: P366458

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8035-F6LBXVM1-WMH-BL87

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	108	104	100	97	106	102	98	95	99	96	93	96	93	91	93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86	91	88	85	88	86	84	82
4	98	91	86	82	96	90	85	81	88	83	80	86	82	79	84	81	78	77
5	93	85	80	76	92	85	79	75	83	78	75	81	77	74	80	76	73	72
6	89	80	75	71	88	80	74	70	78	73	70	77	73	69	76	72	69	68
7	85	76	70	66	83	75	70	66	74	69	65	73	68	65	72	68	65	63
8	81	72	66	62	80	71	66	62	70	65	62	69	65	61	68	64	61	60
9	77	68	62	58	76	67	62	58	66	62	58	66	61	58	65	61	58	56
10	74	64	59	55	73	64	59	55	63	58	55	62	58	55	62	58	55	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	177374
5°	176626
10°	167787
15°	152409
20°	132621
25°	112753
30°	88696
35°	50606
40°	22771
45°	9584
50°	3026
55°	914
60°	628
65°	498
70°	463
75°	612
80°	299
85°	595



TEST NUMBER: P366458

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8035-F6LBXVM1-WMH-BL87

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	602.5	12.0
10°-20°	1499.2	29.7
20°-30°	1698.9	33.7
30°-40°	984.9	19.5
40°-50°	218.4	4.3
50°-60°	23.9	0.5
60°-70°	7.8	0.2
70°-80°	5.1	0.1
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3800.6	75.4
0°-40°	4785.4	94.9
0°-60°	5027.8	99.7
0°-90°	5042.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5042.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6494	
5°	6442	603
15°	5390	1499
25°	3741	1699
35°	1518	985
45°	248	218
55°	19	24
65°	8	8
75°	6	5
85°	2	1
90°	0	



TEST NUMBER: P366458

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8035-F6LBXVM1-WMH-BL87

CANDELA DISTRIBUTION (FULL):

0°	
0°	6493.6
2.5°	6499.4
5°	6441.6
7.5°	6301.2
10°	6049.3
12.5°	5743.4
15°	5389.5
17.5°	5016.4
20°	4562.4
22.5°	4152.7
25°	3741.1
27.5°	3302.6
30°	2812.1
32.5°	2233.1
35°	1517.6
37.5°	975.2
40°	638.6
42.5°	417.4
45°	248.1
47.5°	138.5
50°	71.2
52.5°	32.7
55°	19.2
57.5°	15.4
60°	11.5
62.5°	9.6
65°	7.7
67.5°	5.8
70°	5.8
72.5°	5.8
75°	5.8
77.5°	3.8
80°	1.9
82.5°	1.9
85°	1.9
87.5°	0.0
90°	0.0

(END OF REPORT)