

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365113

Luminaire Tested: **FLD6BX70D010TE-FEU6B67-8035-F6LBXVM1-LI-BTR81**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P365113  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-25)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX70D010TE-FEU6B67-8035-F6LBXVM1-LI-BTR81  
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM POLYCARBONATE, PATTERN 12 0.156", 7000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5278.0 lumens  
Efficiency: N/A  
Efficacy: 71.9 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.19  
Luminous Opening: Circular (Dia: 0.44' x H: 0')  
CIE Type: Direct


Input Watts (W): 73.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P365113

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8035-F6LBXVM1-LI-BTR81

### Luminous Intensity Polar Plot





TEST NUMBER: P365113

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8035-F6LBXVM1-LI-BTR81

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	98		98	96	95		95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86		90	87	84		87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76		82	78	75		80	76	73	72
4	91	81	74	69	89	80	73	68	78	72	68		75	71	67		73	69	66	64
5	85	74	67	61	83	73	66	61	71	65	61		69	64	60		68	63	59	58
6	79	68	61	55	77	67	60	55	66	59	55		64	59	54		63	58	54	52
7	74	63	55	50	73	62	55	50	61	54	50		59	54	49		58	53	49	47
8	70	58	51	46	68	57	50	46	56	50	45		55	49	45		54	49	45	43
9	65	54	47	42	64	53	46	42	52	46	42		51	46	41		50	45	41	40
10	62	50	43	39	61	50	43	38	49	43	38		48	42	38		47	42	38	37

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	196160
5°	210494
10°	226844
15°	233406
20°	231174
25°	217948
30°	197619
35°	172328
40°	144467
45°	116297
50°	89549
55°	65113
60°	44207
65°	29192
70°	19030
75°	14552
80°	12824
85°	15691



TEST NUMBER: P365113

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8035-F6LBXVM1-LI-BTR81

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	285.9	5.4
10°-20°	883.3	16.7
20°-30°	1261.3	23.9
30°-40°	1227.1	23.2
40°-50°	887.6	16.8
50°-60°	475.8	9.0
60°-70°	179.4	3.4
70°-80°	58.9	1.1
80°-90°	18.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2430.5	46.1
0°-40°	3657.6	69.3
0°-60°	5021.0	95.1
0°-90°	5278.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5278.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2740	
5°	2929	286
15°	3149	883
25°	2759	1261
35°	1972	1227
45°	1148	888
55°	522	476
65°	172	179
75°	53	59
85°	19	19
90°	0	



TEST NUMBER: P365113

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8035-F6LBXVM1-LI-BTR81

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2739.6
2.5°	2818.5
5°	2928.6
7.5°	3048.2
10°	3120.0
12.5°	3151.1
15°	3148.7
17.5°	3105.6
20°	3033.9
22.5°	2919.0
25°	2758.7
27.5°	2586.4
30°	2390.2
32.5°	2189.3
35°	1971.5
37.5°	1751.4
40°	1545.6
42.5°	1335.1
45°	1148.5
47.5°	966.6
50°	803.9
52.5°	653.2
55°	521.6
57.5°	409.1
60°	308.7
62.5°	232.1
65°	172.3
67.5°	124.4
70°	90.9
72.5°	69.4
75°	52.6
77.5°	40.7
80°	31.1
82.5°	23.9
85°	19.1
87.5°	9.6
90°	0.0

(END OF REPORT)