

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366463

Luminaire Tested: **FLD6BX60D010TE-FEU6B67-8035-F6LBXVM1-WMH-BTR81**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P366463
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-31)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX60D010TE-FEU6B67-8035-F6LBXVM1-WMH-BTR81
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, WARM HAZE REFLECTOR,
BOTTOM TRIM POLYCARBONATE, PATTERN 12 0.156", 6000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4369.0 lumens
Efficiency: N/A
Efficacy: 75.2 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.19
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 58.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P366463

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8035-F6LBXVM1-WMH-BTR81

Luminous Intensity Polar Plot





TEST NUMBER: P366463

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8035-F6LBXVM1-WMH-BTR81

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76	82	78	74	80	76	73	71
4	91	81	74	69	89	80	73	68	78	72	67	75	71	67	73	69	66	64
5	85	74	67	61	83	73	66	61	71	65	60	69	64	60	68	63	59	57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52
7	74	63	55	50	72	62	55	50	60	54	49	59	53	49	58	53	49	47
8	69	58	51	46	68	57	50	45	56	50	45	55	49	45	54	49	45	43
9	65	54	47	42	64	53	46	42	52	46	41	51	45	41	50	45	41	39
10	62	50	43	38	60	49	43	38	49	42	38	48	42	38	47	42	38	36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	164462
5°	175786
10°	188186
15°	192324
20°	188214
25°	178241
30°	162273
35°	142338
40°	120202
45°	97200
50°	74923
55°	54702
60°	37648
65°	24855
70°	16204
75°	11841
80°	10102
85°	11748



TEST NUMBER: P366463

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8035-F6LBXVM1-WMH-BTR81

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	238.0	5.4
10°-20°	726.5	16.6
20°-30°	1029.4	23.6
30°-40°	1015.3	23.2
40°-50°	744.2	17.0
50°-60°	399.0	9.1
60°-70°	153.3	3.5
70°-80°	48.8	1.1
80°-90°	14.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1993.9	45.6
0°-40°	3009.2	68.9
0°-60°	4152.4	95.0
0°-90°	4369.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4369.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2297	
5°	2446	238
15°	2594	726
25°	2256	1029
35°	1628	1015
45°	960	744
55°	438	399
65°	147	153
75°	43	49
85°	14	14
90°	0	



TEST NUMBER: P366463

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8035-F6LBXVM1-WMH-BTR81

CANDELA DISTRIBUTION (FULL):

0°	
0°	2296.9
2.5°	2349.9
5°	2445.7
7.5°	2535.3
10°	2588.3
12.5°	2606.7
15°	2594.5
17.5°	2545.5
20°	2470.1
22.5°	2374.3
25°	2256.1
27.5°	2109.4
30°	1962.7
32.5°	1803.7
35°	1628.4
37.5°	1461.3
40°	1286.0
42.5°	1125.0
45°	959.9
47.5°	813.2
50°	672.6
52.5°	546.2
55°	438.2
57.5°	342.4
60°	262.9
62.5°	197.7
65°	146.7
67.5°	108.0
70°	77.4
72.5°	59.1
75°	42.8
77.5°	32.6
80°	24.5
82.5°	18.3
85°	14.3
87.5°	8.2
90°	0.0

(END OF REPORT)