

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365116

Luminaire Tested: **FLD6BX70D010TE-FEU6B67-8035-F6LBXVM1-LI-BTR85**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365116
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-24)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX70D010TE-FEU6B67-8035-F6LBXVM1-LI-BTR85
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM POLYCARBONATE, CLEAR 0.187", 7000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5375.0 lumens
Efficiency: N/A
Efficacy: 73.2 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 73.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365116

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8035-F6LBXVM1-LI-BTR85

Luminous Intensity Polar Plot





TEST NUMBER: P365116

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8035-F6LBXVM1-LI-BTR85

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	87		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	91	82	77	73	89	82	76	73	80	76	72		79	75	72		78	74	71	70
7	87	78	73	69	85	77	72	69	76	72	68		75	71	68		74	70	68	66
8	83	74	69	65	82	74	68	65	73	68	65		72	67	64		71	67	64	63
9	79	71	65	62	78	70	65	61	69	65	61		68	64	61		68	64	61	60
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	603274
5°	589529
10°	543481
15°	481363
20°	407540
25°	322873
30°	226895
35°	94499
40°	32425
45°	8658
50°	4768
55°	4444
60°	4081
65°	4032
70°	3978
75°	4592
80°	5896
85°	9776



TEST NUMBER: P365116

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8035-F6LBXVM1-LI-BTR85

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	760.1	14.1
10°-20°	1801.5	33.5
20°-30°	1849.4	34.4
30°-40°	783.1	14.6
40°-50°	96.3	1.8
50°-60°	31.9	0.6
60°-70°	23.5	0.4
70°-80°	18.2	0.3
80°-90°	11.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4411.0	82.1
0°-40°	5194.1	96.6
0°-60°	5322.3	99.0
0°-90°	5375.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5375.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8425	
5°	8202	760
15°	6494	1801
25°	4087	1849
35°	1081	783
45°	86	96
55°	36	32
65°	24	24
75°	17	18
85°	12	11
90°	0	



TEST NUMBER: P365116

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8035-F6LBXVM1-LI-BTR85

CANDELA DISTRIBUTION (FULL):

0°	
0°	8425.4
2.5°	8370.8
5°	8202.1
7.5°	7912.2
10°	7475.0
12.5°	7009.3
15°	6493.7
17.5°	5940.1
20°	5348.5
22.5°	4718.8
25°	4086.8
27.5°	3433.4
30°	2744.3
32.5°	1934.1
35°	1081.1
37.5°	620.1
40°	346.9
42.5°	183.0
45°	85.5
47.5°	49.9
50°	42.8
52.5°	38.0
55°	35.6
57.5°	33.3
60°	28.5
62.5°	26.1
65°	23.8
67.5°	21.4
70°	19.0
72.5°	19.0
75°	16.6
77.5°	16.6
80°	14.3
82.5°	14.3
85°	11.9
87.5°	7.1
90°	0.0

(END OF REPORT)