

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366562

Luminaire Tested: **FLD6BX70D010TE-FEU6B67-8035-F6LBXVM1-WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P366562
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-11)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX70D010TE-FEU6B67-8035-F6LBXVM1-WMH
Description: VANDAL RESISTANT OPEN, WARM HAZE REFLECTOR, 7000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6846.0 lumens
Efficiency: N/A
Efficacy: 93.3 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.84
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 73.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P366562

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8035-F6LBXVM1-WMH

Luminous Intensity Polar Plot





TEST NUMBER: P366562

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8035-F6LBXVM1-WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	91	90	88
3	103	97	93	89	101	96	92	88	93	90	87		91	88	85		89	86	84	82
4	98	91	86	82	97	90	85	82	88	84	81		86	83	80		84	81	79	77
5	94	86	80	76	92	85	80	76	83	79	75		82	78	75		80	77	74	72
6	89	81	75	71	88	80	75	71	79	74	70		77	73	70		76	72	69	68
7	85	76	71	67	84	76	70	66	74	70	66		73	69	66		72	68	65	64
8	81	72	66	63	80	72	66	62	71	66	62		70	65	62		69	65	62	60
9	78	68	63	59	77	68	62	59	67	62	59		66	62	58		65	61	58	57
10	74	65	59	56	73	64	59	56	64	59	55		63	58	55		62	58	55	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	246976
5°	244506
10°	232261
15°	211144
20°	182662
25°	154689
30°	120732
35°	67212
40°	29450
45°	11836
50°	3255
55°	571
60°	393
65°	310
70°	192
75°	253
80°	0
85°	0



TEST NUMBER: P366562

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8035-F6LBXVM1-WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	833.6	12.2
10°-20°	2071.7	30.3
20°-30°	2327.2	34.0
30°-40°	1316.7	19.2
40°-50°	271.4	4.0
50°-60°	19.7	0.3
60°-70°	4.1	0.1
70°-80°	1.6	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5232.5	76.4
0°-40°	6549.2	95.7
0°-60°	6840.3	99.9
0°-90°	6846.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6846.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9042	
5°	8917	834
15°	7466	2072
25°	5132	2327
35°	2016	1317
45°	306	271
55°	12	20
65°	5	4
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P366562

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8035-F6LBXVM1-WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	9041.7
2.5°	9003.4
5°	8917.2
7.5°	8704.1
10°	8373.8
12.5°	7962.0
15°	7466.5
17.5°	6903.9
20°	6283.9
22.5°	5690.2
25°	5132.5
27.5°	4514.8
30°	3827.8
32.5°	3028.2
35°	2015.6
37.5°	1264.0
40°	825.9
42.5°	521.9
45°	306.4
47.5°	162.8
50°	76.6
52.5°	26.3
55°	12.0
57.5°	9.6
60°	7.2
62.5°	4.8
65°	4.8
67.5°	2.4
70°	2.4
72.5°	2.4
75°	2.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)