

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366475

Luminaire Tested: **FLD6BX60D010TE-FEU6B67-8040-F6LBXVM1-WMH-BL86**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P366475  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-47)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX60D010TE-FEU6B67-8040-F6LBXVM1-WMH-BL86  
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, WARM HAZE REFLECTOR, BOTTOM LENS POLYCARBONATE, CLEAR 0.250", 6000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5311.1 lumens  
Efficiency: N/A  
Efficacy: 91.4 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85  
Luminous Opening: Circular (Dia: 0.71' x H: 0')  
CIE Type: Direct


Input Watts (W): 58.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P366475

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8040-F6LBXVM1-WMH-BL86

### Luminous Intensity Polar Plot





TEST NUMBER: P366475

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8040-F6LBXVM1-WMH-BL86

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	108	104	100	97	106	102	98	95	99	96	93	96	93	91	93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86	91	88	85	88	86	84	82
4	98	91	86	82	96	90	85	81	88	83	80	86	82	79	84	81	78	77
5	93	85	80	76	92	85	79	75	83	78	75	81	77	74	80	76	73	72
6	89	80	75	71	88	80	74	70	78	73	70	77	73	69	76	72	69	68
7	85	76	70	66	83	75	70	66	74	69	65	73	68	65	72	68	65	63
8	81	72	66	62	80	71	66	62	70	65	62	69	65	61	68	64	61	60
9	77	68	62	58	76	67	62	58	66	62	58	66	61	58	65	61	58	56
10	74	64	59	55	73	64	59	55	63	58	55	62	58	55	62	58	55	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	186836
5°	186050
10°	176738
15°	160542
20°	139696
25°	118769
30°	93427
35°	53307
40°	23987
45°	10098
50°	3187
55°	967
60°	666
65°	524
70°	487
75°	644
80°	315
85°	627



TEST NUMBER: P366475

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8040-F6LBXVM1-WMH-BL86

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	634.7	12.0
10°-20°	1579.2	29.7
20°-30°	1789.5	33.7
30°-40°	1037.4	19.5
40°-50°	230.1	4.3
50°-60°	25.2	0.5
60°-70°	8.3	0.2
70°-80°	5.4	0.1
80°-90°	1.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4003.4	75.4
0°-40°	5040.8	94.9
0°-60°	5296.1	99.7
0°-90°	5311.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5311.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6840	
5°	6785	635
15°	5677	1579
25°	3941	1789
35°	1599	1037
45°	261	230
55°	20	25
65°	8	8
75°	6	5
85°	2	1
90°	0	



TEST NUMBER: P366475

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8040-F6LBXVM1-WMH-BL86

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	6840.0
2.5°	6846.1
5°	6785.3
7.5°	6637.4
10°	6372.0
12.5°	6049.9
15°	5677.1
17.5°	5284.0
20°	4805.8
22.5°	4374.3
25°	3940.7
27.5°	3478.8
30°	2962.1
32.5°	2352.3
35°	1598.6
37.5°	1027.2
40°	672.7
42.5°	439.7
45°	261.4
47.5°	145.9
50°	75.0
52.5°	34.4
55°	20.3
57.5°	16.2
60°	12.2
62.5°	10.1
65°	8.1
67.5°	6.1
70°	6.1
72.5°	6.1
75°	6.1
77.5°	4.1
80°	2.0
82.5°	2.0
85°	2.0
87.5°	0.0
90°	0.0

(END OF REPORT)