

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365052

Luminaire Tested: **FLD6BX60D010TE-FEU6B67-8050-F6LBXVM1-LI-BL85**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365052
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-43)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX60D010TE-FEU6B67-8050-F6LBXVM1-LI-BL85
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, SPECULAR CLEAR REFLECTOR,
BOTTOM LENS POLYCARBONATE, CLEAR 0.187", 6000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5576.0 lumens
Efficiency: N/A
Efficacy: 96.0 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.82
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 58.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365052

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8050-F6LBXVM1-LI-BL85

Luminous Intensity Polar Plot





TEST NUMBER: P365052

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8050-F6LBXVM1-LI-BL85

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	91	90	88
3	103	97	93	89	101	96	92	88	93	90	87		91	88	85		89	86	84	83
4	99	91	86	82	97	90	85	82	88	84	81		86	83	80		84	81	79	77
5	94	86	80	76	92	85	80	76	83	79	75		82	78	75		80	77	74	73
6	90	81	75	71	88	80	75	71	79	74	71		77	73	70		76	73	70	68
7	85	77	71	67	84	76	71	67	75	70	66		74	69	66		72	69	66	64
8	82	72	67	63	80	72	67	63	71	66	63		70	65	62		69	65	62	61
9	78	69	63	59	77	68	63	59	67	62	59		66	62	59		66	62	59	57
10	74	65	60	56	74	65	60	56	64	59	56		63	59	56		63	58	56	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	214531
5°	210454
10°	194348
15°	173185
20°	147902
25°	124215
30°	97509
35°	50529
40°	24129
45°	9499
50°	2499
55°	700
60°	459
65°	407
70°	335
75°	443
80°	330
85°	658



TEST NUMBER: P365052

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8050-F6LBXVM1-LI-BL85

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	711.7	12.8
10°-20°	1702.1	30.5
20°-30°	1879.2	33.7
30°-40°	1034.1	18.5
40°-50°	218.6	3.9
50°-60°	18.5	0.3
60°-70°	5.7	0.1
70°-80°	4.1	0.1
80°-90°	2.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4293.0	77.0
0°-40°	5327.1	95.5
0°-60°	5564.1	99.8
0°-90°	5576.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5576.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7854	
5°	7675	712
15°	6124	1702
25°	4121	1879
35°	1515	1034
45°	246	219
55°	15	18
65°	6	6
75°	4	4
85°	2	2
90°	0	



TEST NUMBER: P365052

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8050-F6LBXVM1-LI-BL85

CANDELA DISTRIBUTION (FULL):

	0°
0°	7853.9
2.5°	7849.7
5°	7675.3
7.5°	7406.3
10°	7006.9
12.5°	6609.7
15°	6124.2
17.5°	5630.3
20°	5088.1
22.5°	4613.1
25°	4121.4
27.5°	3646.4
30°	3091.5
32.5°	2360.2
35°	1515.3
37.5°	1021.4
40°	676.7
42.5°	422.4
45°	245.9
47.5°	126.1
50°	58.8
52.5°	25.2
55°	14.7
57.5°	10.5
60°	8.4
62.5°	6.3
65°	6.3
67.5°	4.2
70°	4.2
72.5°	6.3
75°	4.2
77.5°	2.1
80°	2.1
82.5°	2.1
85°	2.1
87.5°	2.1
90°	0.0

(END OF REPORT)