

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366568

Luminaire Tested: **FLD6BX70D010TE-FEU6B67-8040-F6LBXVM1-WMH-BL89BV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P366568  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-45)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX70D010TE-FEU6B67-8040-F6LBXVM1-WMH-BL89BV  
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, WARM HAZE REFLECTOR, BOTTOM LENS ACRYLIC, CLEAR 0.125", 7000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6635.0 lumens  
Efficiency: N/A  
Efficacy: 90.4 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85  
Luminous Opening: Circular (Dia: 0.71' x H: 0')  
CIE Type: Direct


Input Watts (W): 73.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P366568

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8040-F6LBXVM1-WMH-BL89BV

### Luminous Intensity Polar Plot





TEST NUMBER: P366568

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8040-F6LBXVM1-WMH-BL89BV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	108	104	100	97	106	102	99	96	99	96	93	96	94	91	93	91	90	88
3	103	97	92	89	101	96	91	88	93	89	86	91	88	85	88	86	84	82
4	98	91	86	82	97	90	85	81	88	84	80	86	82	79	84	81	78	77
5	94	86	80	76	92	85	79	76	83	78	75	81	77	74	80	76	74	72
6	89	81	75	71	88	80	74	71	78	74	70	77	73	70	76	72	69	68
7	85	76	70	66	84	75	70	66	74	69	66	73	69	65	72	68	65	64
8	81	72	66	62	80	71	66	62	70	65	62	69	65	62	68	64	61	60
9	77	68	62	59	76	68	62	58	67	62	58	66	61	58	65	61	58	57
10	74	65	59	55	73	64	59	55	63	58	55	63	58	55	62	58	55	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	235785
5°	234232
10°	222714
15°	202098
20°	175320
25°	149038
30°	117282
35°	66071
40°	29674
45°	12334
50°	3701
55°	1038
60°	661
65°	472
70°	383
75°	507
80°	378
85°	0



TEST NUMBER: P366568

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8040-F6LBXVM1-WMH-BL89BV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	797.7	12.0
10°-20°	1983.6	29.9
20°-30°	2246.1	33.9
30°-40°	1287.8	19.4
40°-50°	279.8	4.2
50°-60°	27.4	0.4
60°-70°	8.1	0.1
70°-80°	4.1	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5027.4	75.8
0°-40°	6315.2	95.2
0°-60°	6622.4	99.8
0°-90°	6635.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6635.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8632	
5°	8542	798
15°	7147	1984
25°	4945	2246
35°	1981	1288
45°	319	280
55°	22	27
65°	7	8
75°	5	4
85°	0	0
90°	0	



TEST NUMBER: P366568

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8040-F6LBXVM1-WMH-BL89BV

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	8632.0
2.5°	8607.8
5°	8542.5
7.5°	8317.5
10°	8029.6
12.5°	7618.3
15°	7146.6
17.5°	6604.6
20°	6031.3
22.5°	5494.2
25°	4945.0
27.5°	4364.4
30°	3718.4
32.5°	2929.7
35°	1981.4
37.5°	1253.2
40°	832.2
42.5°	532.2
45°	319.3
47.5°	174.2
50°	87.1
52.5°	36.3
55°	21.8
57.5°	16.9
60°	12.1
62.5°	9.7
65°	7.3
67.5°	7.3
70°	4.8
72.5°	4.8
75°	4.8
77.5°	2.4
80°	2.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)