

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365054

Luminaire Tested: **FLD6BX60D010TE-FEU6B67-8050-F6LBXVM1-LI-BL87**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365054
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-43)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX60D010TE-FEU6B67-8050-F6LBXVM1-LI-BL87
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, SPECULAR CLEAR REFLECTOR,
BOTTOM LENS POLYCARBONATE, CLEAR 0.375", 6000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5282.1 lumens
Efficiency: N/A
Efficacy: 90.9 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.82
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 58.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365054

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8050-F6LBXVM1-LI-BL87

Luminous Intensity Polar Plot





TEST NUMBER: P365054

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8050-F6LBXVM1-LI-BL87

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	91	90	88
3	103	97	93	89	101	96	92	88	93	90	87		91	88	85		89	86	84	83
4	99	91	86	82	97	90	85	82	88	84	81		86	83	80		84	81	79	77
5	94	86	80	76	92	85	80	76	83	79	75		82	78	75		80	77	74	73
6	90	81	75	71	88	80	75	71	79	74	71		77	73	70		76	73	70	68
7	85	77	71	67	84	76	71	67	75	70	66		74	69	66		72	69	66	64
8	82	72	67	63	80	72	67	63	71	66	63		70	65	62		69	65	62	61
9	78	69	63	59	77	68	63	59	67	62	59		66	62	59		66	62	59	57
10	74	65	60	56	73	65	60	56	64	59	56		63	59	56		63	58	56	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	203220
5°	199357
10°	184102
15°	164054
20°	140103
25°	117666
30°	92368
35°	47865
40°	22860
45°	8997
50°	2367
55°	662
60°	437
65°	388
70°	319
75°	422
80°	315
85°	627



TEST NUMBER: P365054

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8050-F6LBXVM1-LI-BL87

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	674.2	12.8
10°-20°	1612.3	30.5
20°-30°	1780.1	33.7
30°-40°	979.5	18.5
40°-50°	207.1	3.9
50°-60°	17.5	0.3
60°-70°	5.4	0.1
70°-80°	4.0	0.1
80°-90°	1.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4066.6	77.0
0°-40°	5046.2	95.5
0°-60°	5270.8	99.8
0°-90°	5282.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5282.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7440	
5°	7271	674
15°	5801	1612
25°	3904	1780
35°	1435	980
45°	233	207
55°	14	18
65°	6	5
75°	4	4
85°	2	2
90°	0	



TEST NUMBER: P365054

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8050-F6LBXVM1-LI-BL87

CANDELA DISTRIBUTION (FULL):

	0°
0°	7439.8
2.5°	7435.8
5°	7270.6
7.5°	7015.7
10°	6637.5
12.5°	6261.2
15°	5801.3
17.5°	5333.5
20°	4819.8
22.5°	4369.9
25°	3904.1
27.5°	3454.1
30°	2928.5
32.5°	2235.7
35°	1435.4
37.5°	967.6
40°	641.1
42.5°	400.2
45°	232.9
47.5°	119.5
50°	55.7
52.5°	23.9
55°	13.9
57.5°	10.0
60°	8.0
62.5°	6.0
65°	6.0
67.5°	4.0
70°	4.0
72.5°	6.0
75°	4.0
77.5°	2.0
80°	2.0
82.5°	2.0
85°	2.0
87.5°	2.0
90°	0.0

(END OF REPORT)