

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365772

Luminaire Tested: **FLD6BX60D010TE-FEU6B67-8050-F6LBXVM1-MW-BL85**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365772
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-37)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX60D010TE-FEU6B67-8050-F6LBXVM1-MW-BL85
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, MATTE WHITE REFLECTOR, BOTTOM LENS POLYCARBONATE, CLEAR 0.187", 6000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4838.0 lumens
Efficiency: N/A
Efficacy: 83.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.95
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 58.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365772

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8050-F6LBXVM1-MW-BL85

Luminous Intensity Polar Plot





TEST NUMBER: P365772

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8050-F6LBXVM1-MW-BL85

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97		98	96	94		95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86		90	87	84		87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76		82	78	75		80	77	74	72
4	91	82	75	69	89	80	74	69	78	73	68		76	71	67		74	70	67	65
5	85	75	68	63	83	74	67	62	72	66	62		70	65	61		69	64	60	59
6	80	69	62	57	78	68	62	57	67	61	56		65	60	56		64	59	55	54
7	75	64	57	52	74	63	57	52	62	56	51		61	55	51		60	55	51	49
8	71	60	53	48	70	59	52	48	58	52	47		57	51	47		56	51	47	45
9	67	56	49	44	66	55	49	44	54	48	44		53	48	44		52	47	44	42
10	64	52	46	41	62	52	45	41	51	45	41		50	45	41		49	44	41	39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	107100
5°	104732
10°	99333
15°	93105
20°	86874
25°	79905
30°	68453
35°	52116
40°	38278
45°	29007
50°	23750
55°	20892
60°	18667
65°	16359
70°	13984
75°	10902
80°	7299
85°	3291



TEST NUMBER: P365772

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8050-F6LBXVM1-MW-BL85

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	356.9	7.4
10°-20°	924.3	19.1
20°-30°	1204.4	24.9
30°-40°	982.0	20.3
40°-50°	594.5	12.3
50°-60°	394.8	8.2
60°-70°	252.5	5.2
70°-80°	111.9	2.3
80°-90°	16.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2485.6	51.4
0°-40°	3467.6	71.7
0°-60°	4457.0	92.1
0°-90°	4838.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4838.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3921	
5°	3820	357
15°	3292	924
25°	2651	1204
35°	1563	982
45°	751	595
55°	439	395
65°	253	253
75°	103	112
85°	10	17
90°	0	



TEST NUMBER: P365772

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8050-F6LBXVM1-MW-BL85

CANDELA DISTRIBUTION (FULL):

	0°
0°	3920.9
2.5°	3891.4
5°	3819.6
7.5°	3712.1
10°	3581.3
12.5°	3437.9
15°	3292.4
17.5°	3146.8
20°	2988.6
22.5°	2836.8
25°	2651.2
27.5°	2436.0
30°	2170.3
32.5°	1866.6
35°	1562.9
37.5°	1288.7
40°	1073.5
42.5°	890.1
45°	750.9
47.5°	641.2
50°	558.9
52.5°	491.4
55°	438.7
57.5°	388.1
60°	341.7
62.5°	297.4
65°	253.1
67.5°	213.0
70°	175.1
72.5°	137.1
75°	103.3
77.5°	73.8
80°	46.4
82.5°	25.3
85°	10.5
87.5°	2.1
90°	0.0

(END OF REPORT)