

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366595

Luminaire Tested: **FLD6BX70D010TE-FEU6B67-8050-F6LBXVM1-WMH-BTR89BI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P366595
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-28)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX70D010TE-FEU6B67-8050-F6LBXVM1-WMH-BTR89BI
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, WARM HAZE REFLECTOR,
BOTTOM TRIM ACRYLIC, CLEAR RFI 0.125", 7000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5327.0 lumens
Efficiency: N/A
Efficacy: 72.6 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.8
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 73.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P366595

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8050-F6LBXVM1-WMH-BTR89BI

Luminous Intensity Polar Plot





TEST NUMBER: P366595

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8050-F6LBXVM1-WMH-BTR89BI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	92	90	88
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	80	78
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74
6	90	82	76	72	89	81	76	72	80	75	72	78	74	71	77	74	71	69
7	86	78	72	68	85	77	72	68	76	71	68	75	70	67	74	70	67	66
8	82	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62
9	79	70	65	61	78	70	64	61	69	64	61	68	63	60	67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	551793
5°	544341
10°	518150
15°	471037
20°	405612
25°	324240
30°	227350
35°	105757
40°	33415
45°	10440
50°	4589
55°	4294
60°	3938
65°	3490
70°	3831
75°	4426
80°	5649
85°	9448



TEST NUMBER: P366595

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8050-F6LBXVM1-WMH-BTR89BI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	708.9	13.3
10°-20°	1761.9	33.1
20°-30°	1852.3	34.8
30°-40°	821.8	15.4
40°-50°	102.8	1.9
50°-60°	30.7	0.6
60°-70°	21.5	0.4
70°-80°	16.9	0.3
80°-90°	10.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4323.2	81.2
0°-40°	5145.0	96.6
0°-60°	5278.5	99.1
0°-90°	5327.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5327.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7706	
5°	7573	709
15°	6354	1762
25°	4104	1852
35°	1210	822
45°	103	103
55°	34	31
65°	21	22
75°	16	17
85°	12	10
90°	0	



TEST NUMBER: P366595

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8050-F6LBXVM1-WMH-BTR89BI

CANDELA DISTRIBUTION (FULL):

0°	
0°	7706.4
2.5°	7655.9
5°	7573.4
7.5°	7403.9
10°	7126.6
12.5°	6787.5
15°	6354.4
17.5°	5866.3
20°	5323.2
22.5°	4734.3
25°	4104.1
27.5°	3435.0
30°	2749.8
32.5°	2023.4
35°	1209.9
37.5°	643.9
40°	357.5
42.5°	194.8
45°	103.1
47.5°	50.4
50°	41.2
52.5°	36.7
55°	34.4
57.5°	32.1
60°	27.5
62.5°	25.2
65°	20.6
67.5°	18.3
70°	18.3
72.5°	16.0
75°	16.0
77.5°	16.0
80°	13.7
82.5°	11.5
85°	11.5
87.5°	6.9
90°	0.0

(END OF REPORT)