

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P574848

Luminaire Tested: **FLD6C-10-D010 FEU6C-X-90-35 F6X-N-X-H**

Issue Date: 3/1/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P574848  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/1/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6C-10-D010 FEU6C-X-90-35 F6X-N-X-H  
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 6LBNH TRIM

Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 657.0 lumens  
Efficiency: N/A  
Efficacy: 67.4 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.75  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P574848

CATALOG NUMBER: FLD6C-10-D010 FEU6C-X-90-35 F6X-N-X-H

### Luminous Intensity Polar Plot





TEST NUMBER: P574848

CATALOG NUMBER: FLD6C-10-D010 FEU6C-X-90-35 F6X-N-X-H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	46170
5°	45025
10°	41549
15°	36782
20°	31940
25°	27316
30°	22522
35°	14830
40°	7972
45°	3527
50°	1433
55°	1032
60°	658
65°	467
70°	385
75°	254
80°	379
85°	0



TEST NUMBER: P574848

CATALOG NUMBER: FLD6C-10-D010 FEU6C-X-90-35 F6X-N-X-H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	75.7	11.5
10°-20°	180.6	27.5
20°-30°	206.9	31.5
30°-40°	139.0	21.2
40°-50°	39.7	6.0
50°-60°	9.7	1.5
60°-70°	3.7	0.6
70°-80°	1.4	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	463.2	70.5
0°-40°	602.3	91.7
0°-60°	651.7	99.2
0°-90°	657.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	657.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	842	
5°	818	76
15°	648	181
25°	452	207
35°	222	139
45°	46	40
55°	11	10
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P574848

CATALOG NUMBER: FLD6C-10-D010 FEU6C-X-90-35 F6X-N-X-H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	842.2
2.5°	836.2
5°	818.2
7.5°	785.9
10°	746.4
12.5°	696.0
15°	648.1
17.5°	597.8
20°	547.5
22.5°	499.6
25°	451.6
27.5°	407.3
30°	355.8
32.5°	287.5
35°	221.6
37.5°	161.7
40°	111.4
42.5°	73.1
45°	45.5
47.5°	27.5
50°	16.8
52.5°	13.2
55°	10.8
57.5°	8.4
60°	6.0
62.5°	4.8
65°	3.6
67.5°	2.4
70°	2.4
72.5°	1.2
75°	1.2
77.5°	1.2
80°	1.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC







— 0°-180°







(END OF REPORT)