

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366548

Luminaire Tested: **FLD6BX70D010TE-FEU6B67-8035-F6LBXVM1-WMH-BL87**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P366548
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-47)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX70D010TE-FEU6B67-8035-F6LBXVM1-WMH-BL87
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, WARM HAZE REFLECTOR, BOTTOM LENS POLYCARBONATE, CLEAR 0.375", 7000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5922.1 lumens
Efficiency: N/A
Efficacy: 80.7 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 73.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P366548

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8035-F6LBXVM1-WMH-BL87

Luminous Intensity Polar Plot





TEST NUMBER: P366548

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8035-F6LBXVM1-WMH-BL87

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	108	104	100	97	106	102	98	95	99	96	93	96	93	91	93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86	91	88	85	88	86	84	82
4	98	91	86	82	96	90	85	81	88	83	80	86	82	79	84	81	78	77
5	93	85	80	76	92	85	79	75	83	78	75	81	77	74	80	76	73	72
6	89	80	75	71	88	80	74	70	78	73	70	77	73	69	76	72	69	68
7	85	76	70	66	83	75	70	66	74	69	65	73	68	65	72	68	65	63
8	81	72	66	62	80	71	66	62	70	65	62	69	65	61	68	64	61	60
9	77	68	62	58	76	67	62	58	66	62	58	66	61	58	65	61	58	56
10	74	64	59	55	73	64	59	55	63	58	55	62	58	55	62	58	55	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	208331
5°	207454
10°	197072
15°	179011
20°	155768
25°	132434
30°	104177
35°	59439
40°	26743
45°	11257
50°	3553
55°	1076
60°	743
65°	582
70°	543
75°	718
80°	362
85°	721



TEST NUMBER: P366548

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8035-F6LBXVM1-WMH-BL87

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	707.7	12.0
10°-20°	1760.9	29.7
20°-30°	1995.4	33.7
30°-40°	1156.8	19.5
40°-50°	256.5	4.3
50°-60°	28.1	0.5
60°-70°	9.2	0.2
70°-80°	6.0	0.1
80°-90°	1.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4463.9	75.4
0°-40°	5620.7	94.9
0°-60°	5905.3	99.7
0°-90°	5922.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5922.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7627	
5°	7566	708
15°	6330	1761
25°	4394	1995
35°	1782	1157
45°	291	257
55°	23	28
65°	9	9
75°	7	6
85°	2	2
90°	0	



TEST NUMBER: P366548

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8035-F6LBXVM1-WMH-BL87

CANDELA DISTRIBUTION (FULL):

0°	
0°	7626.9
2.5°	7633.7
5°	7565.9
7.5°	7401.0
10°	7105.1
12.5°	6745.9
15°	6330.2
17.5°	5891.9
20°	5358.7
22.5°	4877.5
25°	4394.1
27.5°	3879.0
30°	3302.9
32.5°	2622.9
35°	1782.5
37.5°	1145.4
40°	750.0
42.5°	490.2
45°	291.4
47.5°	162.7
50°	83.6
52.5°	38.4
55°	22.6
57.5°	18.1
60°	13.6
62.5°	11.3
65°	9.0
67.5°	6.8
70°	6.8
72.5°	6.8
75°	6.8
77.5°	4.5
80°	2.3
82.5°	2.3
85°	2.3
87.5°	0.0
90°	0.0

(END OF REPORT)