

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P575338

Luminaire Tested: **FLD6C-120-D010 FEU6C-X-90-27 F6X-N-X-LI**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P575338
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6C-120-D010 FEU6C-X-90-27 F6X-N-X-LI
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 2700K, 90 CRI LEDS, 6LBNLI TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9852.0 lumens
Efficiency: N/A
Efficacy: 69.2 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 142.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P575338

CATALOG NUMBER: FLD6C-120-D010 FEU6C-X-90-27 F6X-N-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P575338

CATALOG NUMBER: FLD6C-120-D010 FEU6C-X-90-27 F6X-N-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89			
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85			
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80			
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76			
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72			
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68			
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65			
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62			
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1229655
5°	1149936
10°	937858
15°	690140
20°	475691
25°	353149
30°	265269
35°	165420
40°	80293
45°	27545
50°	3616
55°	2733
60°	1568
65°	1855
70°	2292
75°	0
80°	0
85°	0



TEST NUMBER: P575338

CATALOG NUMBER: FLD6C-120-D010 FEU6C-X-90-27 F6X-N-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1864.9	18.9
10°-20°	3347.4	34.0
20°-30°	2706.5	27.5
30°-40°	1559.1	15.8
40°-50°	329.6	3.3
50°-60°	28.5	0.3
60°-70°	14.2	0.1
70°-80°	1.9	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7918.8	80.4
0°-40°	9477.9	96.2
0°-60°	9836.0	99.8
0°-90°	9852.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9852.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	22431	
5°	20897	###
15°	12160	3347
25°	5838	2706
35°	2472	1559
45°	355	330
55°	29	28
65°	14	14
75°	0	2
85°	0	0
90°	0	



TEST NUMBER: P575338

CATALOG NUMBER: FLD6C-120-D010 FEU6C-X-90-27 F6X-N-X-LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	22430.7
2.5°	22161.1
5°	20896.7
7.5°	19078.3
10°	16848.0
12.5°	14561.1
15°	12160.2
17.5°	9844.7
20°	8154.0
22.5°	6861.4
25°	5838.4
27.5°	4972.1
30°	4190.6
32.5°	3324.3
35°	2471.8
37.5°	1718.8
40°	1122.0
42.5°	682.0
45°	355.3
47.5°	141.9
50°	42.4
52.5°	42.4
55°	28.6
57.5°	28.6
60°	14.3
62.5°	14.3
65°	14.3
67.5°	14.3
70°	14.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)