

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P575378

Luminaire Tested: **FLD6C-120-D010 FEU6C-X-90-30 F6X-M-X-LI**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P575378
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6C-120-D010 FEU6C-X-90-30 F6X-M-X-LI
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 6LBMLI TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11526.0 lumens
Efficiency: N/A
Efficacy: 81.0 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 142.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P575378

CATALOG NUMBER: FLD6C-120-D010 FEU6C-X-90-30 F6X-M-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P575378

CATALOG NUMBER: FLD6C-120-D010 FEU6C-X-90-30 F6X-M-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94			
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82			
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76			
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71			
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67			
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63			
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	790737
5°	783214
10°	742171
15°	673823
20°	595419
25°	514760
30°	402378
35°	246765
40°	126659
45°	50315
50°	16341
55°	5629
60°	4824
65°	3853
70°	2388
75°	3156
80°	0
85°	0



TEST NUMBER: P575378

CATALOG NUMBER: FLD6C-120-D010 FEU6C-X-90-30 F6X-M-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1328.8	11.5
10°-20°	3308.2	28.7
20°-30°	3845.6	33.4
30°-40°	2355.0	20.4
40°-50°	584.8	5.1
50°-60°	68.3	0.6
60°-70°	25.6	0.2
70°-80°	9.8	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8482.6	73.6
0°-40°	10837.6	94.0
0°-60°	11490.7	99.7
0°-90°	11526.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	11526.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	14424	
5°	14233	###
15°	11873	3308
25°	8510	3846
35°	3687	2355
45°	649	585
55°	59	68
65°	30	26
75°	15	10
85°	0	0
90°	0	



TEST NUMBER: P575378

CATALOG NUMBER: FLD6C-120-D010 FEU6C-X-90-30 F6X-M-X-LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	14424.2
2.5°	14409.4
5°	14232.6
7.5°	13849.0
10°	13332.6
12.5°	12654.4
15°	11872.7
17.5°	11032.0
20°	10206.3
22.5°	9380.0
25°	8510.2
27.5°	7507.2
30°	6356.6
32.5°	5014.5
35°	3687.3
37.5°	2595.6
40°	1769.9
42.5°	1106.0
45°	649.0
47.5°	368.8
50°	191.6
52.5°	88.6
55°	58.9
57.5°	44.0
60°	44.0
62.5°	29.7
65°	29.7
67.5°	14.9
70°	14.9
72.5°	14.9
75°	14.9
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)