

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P575468

Luminaire Tested: **FLD6C-120-D010 FEU6C-X-90-35 F6X-W-X-H**

Issue Date: 3/1/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P575468  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/1/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6C-120-D010 FEU6C-X-90-35 F6X-W-X-H  
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 6LBWH TRIM

Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 11557.0 lumens  
Efficiency: N/A  
Efficacy: 81.2 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 142.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P575468

CATALOG NUMBER: FLD6C-120-D010 FEU6C-X-90-35 F6X-W-X-H

### Luminous Intensity Polar Plot





TEST NUMBER: P575468

CATALOG NUMBER: FLD6C-120-D010 FEU6C-X-90-35 F6X-W-X-H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91			91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			81
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73			73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			65
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59			59
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			53
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49			49
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41			41
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38			38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	390753
5°	390616
10°	387613
15°	385014
20°	379153
25°	370485
30°	348838
35°	315696
40°	263615
45°	201998
50°	143057
55°	90195
60°	50873
65°	33026
70°	21574
75°	15843
80°	9502
85°	9498



TEST NUMBER: P575468

CATALOG NUMBER: FLD6C-120-D010 FEU6C-X-90-35 F6X-W-X-H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	673.2	5.8
10°-20°	1910.3	16.5
20°-30°	2801.0	24.2
30°-40°	2915.1	25.2
40°-50°	2016.8	17.5
50°-60°	878.2	7.6
60°-70°	269.3	2.3
70°-80°	80.7	0.7
80°-90°	12.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5384.5	46.6
0°-40°	8299.7	71.8
0°-60°	11194.6	96.9
0°-90°	11557.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	11557.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7128	
5°	7098	673
15°	6784	1910
25°	6125	2801
35°	4717	2915
45°	2606	2017
55°	944	878
65°	255	269
75°	75	81
85°	15	12
90°	0	



TEST NUMBER: P575468

CATALOG NUMBER: FLD6C-120-D010 FEU6C-X-90-35 F6X-W-X-H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	7127.9
2.5°	7143.0
5°	7098.3
7.5°	7038.6
10°	6963.2
12.5°	6888.4
15°	6783.9
17.5°	6648.8
20°	6499.2
22.5°	6334.4
25°	6125.0
27.5°	5855.3
30°	5510.8
32.5°	5151.2
35°	4717.3
37.5°	4238.2
40°	3683.7
42.5°	3129.8
45°	2605.5
47.5°	2111.3
50°	1677.4
52.5°	1273.1
55°	943.7
57.5°	674.0
60°	464.0
62.5°	344.5
65°	254.6
67.5°	194.9
70°	134.6
72.5°	105.0
75°	74.8
77.5°	44.7
80°	30.1
82.5°	15.1
85°	15.1
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC







— 0°-180°







(END OF REPORT)