

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365123

Luminaire Tested: **FLD6BX70D010TE-FEU6B67-8040-F6LBXVM1-LI-BL84**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365123
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-43)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX70D010TE-FEU6B67-8040-F6LBXVM1-LI-BL84
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, SPECULAR CLEAR REFLECTOR,
BOTTOM LENS POLYCARBONATE, CLEAR 0.125", 7000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6416.9 lumens
Efficiency: N/A
Efficacy: 87.4 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.82
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 73.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365123

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8040-F6LBXVM1-LI-BL84

Luminous Intensity Polar Plot





TEST NUMBER: P365123

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8040-F6LBXVM1-LI-BL84

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	91	90	88
3	103	97	93	89	101	96	92	88	93	90	87		91	88	85		89	86	84	83
4	99	91	86	82	97	90	85	82	88	84	81		86	83	80		84	81	79	77
5	94	86	80	76	92	85	80	76	83	79	75		82	78	75		80	77	74	73
6	90	81	75	71	88	80	75	71	79	74	71		77	73	70		76	73	70	68
7	85	77	71	67	84	76	71	67	75	70	66		74	69	66		72	69	66	64
8	82	72	67	63	80	72	67	63	71	66	63		70	65	62		69	65	62	61
9	78	69	63	59	77	68	63	59	67	62	59		66	62	59		66	62	59	57
10	74	65	60	56	74	65	60	56	64	59	56		63	59	56		63	58	56	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	246889
5°	242195
10°	223663
15°	199306
20°	170209
25°	142950
30°	112216
35°	58148
40°	27770
45°	10932
50°	2877
55°	805
60°	530
65°	472
70°	383
75°	507
80°	378
85°	752



TEST NUMBER: P365123

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8040-F6LBXVM1-LI-BL84

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	819.1	12.8
10°-20°	1958.8	30.5
20°-30°	2162.7	33.7
30°-40°	1190.0	18.5
40°-50°	251.5	3.9
50°-60°	21.3	0.3
60°-70°	6.6	0.1
70°-80°	4.8	0.1
80°-90°	2.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4940.5	77.0
0°-40°	6130.5	95.5
0°-60°	6403.3	99.8
0°-90°	6416.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6416.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9038	
5°	8833	819
15°	7048	1959
25°	4743	2163
35°	1744	1190
45°	283	252
55°	17	21
65°	7	7
75°	5	5
85°	2	2
90°	0	



TEST NUMBER: P365123

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8040-F6LBXVM1-LI-BL84

CANDELA DISTRIBUTION (FULL):

	0°
0°	9038.5
2.5°	9033.6
5°	8832.9
7.5°	8523.3
10°	8063.8
12.5°	7606.6
15°	7047.9
17.5°	6479.5
20°	5855.5
22.5°	5308.9
25°	4743.0
27.5°	4196.3
30°	3557.8
32.5°	2716.1
35°	1743.8
37.5°	1175.5
40°	778.8
42.5°	486.1
45°	283.0
47.5°	145.1
50°	67.7
52.5°	29.0
55°	16.9
57.5°	12.1
60°	9.7
62.5°	7.3
65°	7.3
67.5°	4.8
70°	4.8
72.5°	7.3
75°	4.8
77.5°	2.4
80°	2.4
82.5°	2.4
85°	2.4
87.5°	2.4
90°	0.0

(END OF REPORT)