

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365136

Luminaire Tested: **FLD6BX70D010TE-FEU6B67-8040-F6LBXVM1-LI-BTR87**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P365136  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-24)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX70D010TE-FEU6B67-8040-F6LBXVM1-LI-BTR87  
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM POLYCARBONATE, CLEAR 0.375", 7000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5358.0 lumens  
Efficiency: N/A  
Efficacy: 73.0 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77  
Luminous Opening: Circular (Dia: 0.44' x H: 0')  
CIE Type: Direct


Input Watts (W): 73.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P365136

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8040-F6LBXVM1-LI-BTR87

### Luminous Intensity Polar Plot





TEST NUMBER: P365136

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8040-F6LBXVM1-LI-BTR87

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	87		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	91	82	77	73	89	82	76	73	80	76	72		79	75	72		78	74	71	70
7	87	78	73	69	85	77	72	69	76	72	68		75	71	68		74	70	68	66
8	83	74	69	65	82	74	68	65	73	68	65		72	67	64		71	67	64	63
9	79	71	65	62	78	70	65	61	69	65	61		68	64	61		68	64	61	60
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58	57

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	601370
5°	587660
10°	541765
15°	479843
20°	406245
25°	321854
30°	226176
35°	94201
40°	32322
45°	8638
50°	4745
55°	4432
60°	4067
65°	4015
70°	3957
75°	4592
80°	5855
85°	9694



TEST NUMBER: P365136

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8040-F6LBXVM1-LI-BTR87

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	757.7	14.1
10°-20°	1795.8	33.5
20°-30°	1843.5	34.4
30°-40°	780.7	14.6
40°-50°	96.0	1.8
50°-60°	31.8	0.6
60°-70°	23.5	0.4
70°-80°	18.1	0.3
80°-90°	10.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4397.0	82.1
0°-40°	5177.7	96.6
0°-60°	5305.4	99.0
0°-90°	5358.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5358.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8399	
5°	8176	758
15°	6473	1796
25°	4074	1844
35°	1078	781
45°	85	96
55°	36	32
65°	24	23
75°	17	18
85°	12	11
90°	0	



TEST NUMBER: P365136

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8040-F6LBXVM1-LI-BTR87

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	8398.8
2.5°	8344.3
5°	8176.1
7.5°	7887.2
10°	7451.4
12.5°	6987.1
15°	6473.2
17.5°	5921.3
20°	5331.5
22.5°	4703.9
25°	4073.9
27.5°	3422.5
30°	2735.6
32.5°	1928.0
35°	1077.7
37.5°	618.2
40°	345.8
42.5°	182.4
45°	85.3
47.5°	49.7
50°	42.6
52.5°	37.9
55°	35.5
57.5°	33.2
60°	28.4
62.5°	26.1
65°	23.7
67.5°	21.3
70°	18.9
72.5°	18.9
75°	16.6
77.5°	16.6
80°	14.2
82.5°	14.2
85°	11.8
87.5°	7.1
90°	0.0

(END OF REPORT)