

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P575848

Luminaire Tested: **FLD6C-15-D010 FEU6C-X-90-50 F6X-M-X-H**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P575848
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203254)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6C-15-D010 FEU6C-X-90-50 F6X-M-X-H
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 5000K, 90 CRI LEDS, 6LBMH TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1196.0 lumens
Efficiency: N/A
Efficacy: 75.7 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P575848

CATALOG NUMBER: FLD6C-15-D010 FEU6C-X-90-50 F6X-M-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P575848

CATALOG NUMBER: FLD6C-15-D010 FEU6C-X-90-50 F6X-M-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92																																				
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85																																				
3	101	94	88	84	99	92	87	84	90	86	82	87	84	81	85	82	80	78																																				
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72																																				
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66																																				
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61																																				
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																																				
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53																																				
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49																																				
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	64885
5°	63724
10°	60470
15°	56703
20°	52808
25°	48656
30°	40544
35°	28576
40°	18213
45°	10862
50°	6413
55°	4081
60°	2807
65°	1998
70°	1378
75°	1080
80°	537
85°	0



TEST NUMBER: P575848

CATALOG NUMBER: FLD6C-15-D010 FEU6C-X-90-50 F6X-M-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.2	9.0
10°-20°	280.0	23.4
20°-30°	362.8	30.3
30°-40°	269.3	22.5
40°-50°	113.7	9.5
50°-60°	40.4	3.4
60°-70°	15.6	1.3
70°-80°	5.4	0.4
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	750.9	62.8
0°-40°	1020.3	85.3
0°-60°	1174.4	98.2
0°-90°	1196.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1196.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1184	
5°	1158	108
15°	999	280
25°	804	363
35°	427	269
45°	140	114
55°	43	40
65°	15	16
75°	5	5
85°	0	1
90°	0	



TEST NUMBER: P575848

CATALOG NUMBER: FLD6C-15-D010 FEU6C-X-90-50 F6X-M-X-H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1183.6
2.5°	1180.2
5°	1158.0
7.5°	1125.5
10°	1086.3
12.5°	1043.5
15°	999.1
17.5°	949.6
20°	905.2
22.5°	859.1
25°	804.4
27.5°	729.3
30°	640.5
32.5°	536.3
35°	427.0
37.5°	334.8
40°	254.5
42.5°	189.6
45°	140.1
47.5°	102.5
50°	75.2
52.5°	56.4
55°	42.7
57.5°	32.4
60°	25.6
62.5°	18.8
65°	15.4
67.5°	11.9
70°	8.6
72.5°	6.8
75°	5.1
77.5°	3.4
80°	1.7
82.5°	1.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)