

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573808

Luminaire Tested: **FLD6C-02-D010 FEU6C-X-90-27 F6X-M-X-H**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573808
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203254)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6C-02-D010 FEU6C-X-90-27 F6X-M-X-H
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 2700K, 90 CRI LEDS, 6LBMH TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 236.0 lumens
Efficiency: N/A
Efficacy: 67.4 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 3.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573808

CATALOG NUMBER: FLD6C-02-D010 FEU6C-X-90-27 F6X-M-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P573808

CATALOG NUMBER: FLD6C-02-D010 FEU6C-X-90-27 F6X-M-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92				92
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85				85
3	101	94	88	84	99	92	88	84	90	86	82	87	84	81	85	82	80	78				78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72				72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66				66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61				61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57				57
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53				53
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49				49
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46				46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	12806
5°	12574
10°	11935
15°	11192
20°	10419
25°	9599
30°	8001
35°	5642
40°	3592
45°	2140
50°	1262
55°	803
60°	559
65°	389
70°	272
75°	212
80°	95
85°	0



TEST NUMBER: P573808

CATALOG NUMBER: FLD6C-02-D010 FEU6C-X-90-27 F6X-M-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	21.4	9.1
10°-20°	55.2	23.4
20°-30°	71.6	30.3
30°-40°	53.2	22.5
40°-50°	22.4	9.5
50°-60°	8.0	3.4
60°-70°	3.1	1.3
70°-80°	1.1	0.4
80°-90°	0.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	148.2	62.8
0°-40°	201.3	85.3
0°-60°	231.7	98.2
0°-90°	236.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	236.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	234	
5°	228	21
15°	197	55
25°	159	72
35°	84	53
45°	28	22
55°	8	8
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P573808

CATALOG NUMBER: FLD6C-02-D010 FEU6C-X-90-27 F6X-M-X-H

CANDELA DISTRIBUTION (FULL):

	0°
0°	233.6
2.5°	232.9
5°	228.5
7.5°	222.1
10°	214.4
12.5°	205.9
15°	197.2
17.5°	187.4
20°	178.6
22.5°	169.5
25°	158.7
27.5°	143.9
30°	126.4
32.5°	105.8
35°	84.3
37.5°	66.1
40°	50.2
42.5°	37.4
45°	27.6
47.5°	20.2
50°	14.8
52.5°	11.1
55°	8.4
57.5°	6.4
60°	5.1
62.5°	3.7
65°	3.0
67.5°	2.4
70°	1.7
72.5°	1.3
75°	1.0
77.5°	0.7
80°	0.3
82.5°	0.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)