

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573848

Luminaire Tested: **FLD6C-02-D010 FEU6C-X-90-27 F6X-W-X-H**

Issue Date: 3/1/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P573848  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/1/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6C-02-D010 FEU6C-X-90-27 F6X-W-X-H  
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 2700K, 90 CRI LEDS, 6LBWH TRIM

Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 286.0 lumens  
Efficiency: N/A  
Efficacy: 81.7 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 3.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P573848

CATALOG NUMBER: FLD6C-02-D010 FEU6C-X-90-27 F6X-W-X-H

### Luminous Intensity Polar Plot





TEST NUMBER: P573848

CATALOG NUMBER: FLD6C-02-D010 FEU6C-X-90-27 F6X-W-X-H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91			
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73			
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59			
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49			
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41			
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	9670
5°	9669
10°	9591
15°	9529
20°	9381
25°	9170
30°	8634
35°	7810
40°	6527
45°	5001
50°	3539
55°	2236
60°	1261
65°	817
70°	529
75°	402
80°	221
85°	252



TEST NUMBER: P573848

CATALOG NUMBER: FLD6C-02-D010 FEU6C-X-90-27 F6X-W-X-H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	16.7	5.8
10°-20°	47.3	16.5
20°-30°	69.3	24.2
30°-40°	72.1	25.2
40°-50°	49.9	17.5
50°-60°	21.7	7.6
60°-70°	6.7	2.3
70°-80°	2.0	0.7
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	133.3	46.6
0°-40°	205.4	71.8
0°-60°	277.1	96.9
0°-90°	286.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	286.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	176	
5°	176	17
15°	168	47
25°	152	69
35°	117	72
45°	64	50
55°	23	22
65°	6	7
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P573848

CATALOG NUMBER: FLD6C-02-D010 FEU6C-X-90-27 F6X-W-X-H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	176.4
2.5°	176.8
5°	175.7
7.5°	174.2
10°	172.3
12.5°	170.5
15°	167.9
17.5°	164.5
20°	160.8
22.5°	156.8
25°	151.6
27.5°	144.9
30°	136.4
32.5°	127.5
35°	116.7
37.5°	104.9
40°	91.2
42.5°	77.5
45°	64.5
47.5°	52.2
50°	41.5
52.5°	31.5
55°	23.4
57.5°	16.7
60°	11.5
62.5°	8.5
65°	6.3
67.5°	4.8
70°	3.3
72.5°	2.6
75°	1.9
77.5°	1.1
80°	0.7
82.5°	0.4
85°	0.4
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC







— 0°-180°







(END OF REPORT)