

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366565

Luminaire Tested: **FLD6BX70D010TE-FEU6B67-8040-F6LBXVM1-WMH-BL86**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P366565
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-47)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX70D010TE-FEU6B67-8040-F6LBXVM1-WMH-BL86
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, WARM HAZE REFLECTOR, BOTTOM LENS POLYCARBONATE, CLEAR 0.250", 7000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6238.0 lumens
Efficiency: N/A
Efficacy: 85.0 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 73.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P366565

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8040-F6LBXVM1-WMH-BL86

Luminous Intensity Polar Plot





TEST NUMBER: P366565

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8040-F6LBXVM1-WMH-BL86

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	108	104	100	97	106	102	98	95	99	96	93	96	93	91	93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86	91	88	85	88	86	84	82
4	98	91	86	82	96	90	85	81	88	83	80	86	82	79	84	81	78	77
5	93	85	80	76	92	85	79	75	83	78	75	81	77	74	80	76	73	72
6	89	80	75	71	88	80	74	70	78	73	70	77	73	69	76	72	69	68
7	85	76	70	66	83	75	70	66	74	69	65	73	68	65	72	68	65	63
8	81	72	66	62	80	71	66	62	70	65	62	69	65	61	68	64	61	60
9	77	68	62	58	76	67	62	58	66	62	58	66	61	58	65	61	58	56
10	74	64	59	55	73	64	59	55	63	58	55	62	58	55	62	58	55	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	219448
5°	218526
10°	207587
15°	188563
20°	164082
25°	139499
30°	109734
35°	62610
40°	28173
45°	11859
50°	3740
55°	1133
60°	781
65°	614
70°	567
75°	749
80°	378
85°	752



TEST NUMBER: P366565

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8040-F6LBXVM1-WMH-BL86

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	745.5	12.0
10°-20°	1854.8	29.7
20°-30°	2101.8	33.7
30°-40°	1218.5	19.5
40°-50°	270.2	4.3
50°-60°	29.6	0.5
60°-70°	9.7	0.2
70°-80°	6.3	0.1
80°-90°	1.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4702.1	75.4
0°-40°	5920.6	94.9
0°-60°	6220.4	99.7
0°-90°	6238.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6238.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8034	
5°	7970	745
15°	6668	1855
25°	4628	2102
35°	1878	1218
45°	307	270
55°	24	30
65°	10	10
75°	7	6
85°	2	2
90°	0	



TEST NUMBER: P366565

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8040-F6LBXVM1-WMH-BL86

CANDELA DISTRIBUTION (FULL):

0°	
0°	8033.9
2.5°	8041.0
5°	7969.7
7.5°	7795.9
10°	7484.2
12.5°	7105.8
15°	6668.0
17.5°	6206.3
20°	5644.7
22.5°	5137.8
25°	4628.5
27.5°	4086.0
30°	3479.1
32.5°	2762.8
35°	1877.6
37.5°	1206.5
40°	790.1
42.5°	516.4
45°	307.0
47.5°	171.3
50°	88.0
52.5°	40.5
55°	23.8
57.5°	19.0
60°	14.3
62.5°	11.9
65°	9.5
67.5°	7.1
70°	7.1
72.5°	7.1
75°	7.1
77.5°	4.8
80°	2.4
82.5°	2.4
85°	2.4
87.5°	0.0
90°	0.0

(END OF REPORT)