

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573868

Luminaire Tested: **FLD6C-02-D010 FEU6C-X-90-30 F6X-M-X-H**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573868
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203254)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6C-02-D010 FEU6C-X-90-30 F6X-M-X-H
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 6LBMH TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 246.0 lumens
Efficiency: N/A
Efficacy: 70.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 3.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573868

CATALOG NUMBER: FLD6C-02-D010 FEU6C-X-90-30 F6X-M-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P573868

CATALOG NUMBER: FLD6C-02-D010 FEU6C-X-90-30 F6X-M-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92			92
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72			72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66			66
6	85	75	69	64	83	75	68	64	73	68	64	72	67	63	70	66	63	61			61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			57
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53			53
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49			49
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46			46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	13349
5°	13108
10°	12436
15°	11663
20°	10863
25°	10011
30°	8337
35°	5876
40°	3743
45°	2233
50°	1322
55°	841
60°	581
65°	415
70°	289
75°	233
80°	95
85°	0



TEST NUMBER: P573868

CATALOG NUMBER: FLD6C-02-D010 FEU6C-X-90-30 F6X-M-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	22.3	9.0
10°-20°	57.6	23.4
20°-30°	74.6	30.3
30°-40°	55.4	22.5
40°-50°	23.4	9.5
50°-60°	8.3	3.4
60°-70°	3.2	1.3
70°-80°	1.1	0.5
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	154.5	62.8
0°-40°	209.8	85.3
0°-60°	241.6	98.2
0°-90°	246.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	246.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	244	
5°	238	22
15°	206	58
25°	166	75
35°	88	55
45°	29	23
55°	9	8
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P573868

CATALOG NUMBER: FLD6C-02-D010 FEU6C-X-90-30 F6X-M-X-H

CANDELA DISTRIBUTION (FULL):

	0°
0°	243.5
2.5°	242.7
5°	238.2
7.5°	231.5
10°	223.4
12.5°	214.6
15°	205.5
17.5°	195.3
20°	186.2
22.5°	176.7
25°	165.5
27.5°	150.0
30°	131.7
32.5°	110.3
35°	87.8
37.5°	68.9
40°	52.3
42.5°	39.0
45°	28.8
47.5°	21.1
50°	15.5
52.5°	11.6
55°	8.8
57.5°	6.7
60°	5.3
62.5°	3.9
65°	3.2
67.5°	2.5
70°	1.8
72.5°	1.4
75°	1.1
77.5°	0.7
80°	0.3
82.5°	0.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)