

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366566

Luminaire Tested: **FLD6BX70D010TE-FEU6B67-8040-F6LBXVM1-WMH-BL87**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P366566  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-47)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX70D010TE-FEU6B67-8040-F6LBXVM1-WMH-BL87  
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, WARM HAZE REFLECTOR, BOTTOM LENS POLYCARBONATE, CLEAR 0.375", 7000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5984.9 lumens  
Efficiency: N/A  
Efficacy: 81.5 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85  
Luminous Opening: Circular (Dia: 0.71' x H: 0')  
CIE Type: Direct


Input Watts (W): 73.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P366566

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8040-F6LBXVM1-WMH-BL87

### Luminous Intensity Polar Plot





TEST NUMBER: P366566

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8040-F6LBXVM1-WMH-BL87

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	108	104	100	97	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86		91	88	85		88	86	84	82
4	98	91	86	82	96	90	85	81	88	83	80		86	82	79		84	81	78	77
5	93	85	80	76	92	85	79	75	83	78	75		81	77	74		80	76	73	72
6	89	80	75	71	88	80	74	70	78	73	70		77	73	69		76	72	69	68
7	85	76	70	66	83	75	70	66	74	69	65		73	68	65		72	68	65	63
8	81	72	66	62	80	71	66	62	70	65	62		69	65	61		68	64	61	60
9	77	68	62	58	76	67	62	58	66	62	58		66	61	58		65	61	58	56
10	74	64	59	55	73	64	59	55	63	58	55		62	58	55		62	58	55	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	210549
5°	209661
10°	199169
15°	180914
20°	157425
25°	133842
30°	105284
35°	60069
40°	27028
45°	11376
50°	3591
55°	1086
60°	748
65°	588
70°	543
75°	718
80°	362
85°	721



TEST NUMBER: P366566

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8040-F6LBXVM1-WMH-BL87

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	715.2	12.0
10°-20°	1779.6	29.7
20°-30°	2016.6	33.7
30°-40°	1169.1	19.5
40°-50°	259.2	4.3
50°-60°	28.4	0.5
60°-70°	9.3	0.2
70°-80°	6.0	0.1
80°-90°	1.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4511.4	75.4
0°-40°	5680.4	94.9
0°-60°	5968.1	99.7
0°-90°	5984.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5984.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7708	
5°	7646	715
15°	6398	1780
25°	4441	2017
35°	1801	1169
45°	294	259
55°	23	28
65°	9	9
75°	7	6
85°	2	2
90°	0	



TEST NUMBER: P366566

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8040-F6LBXVM1-WMH-BL87

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	7708.1
2.5°	7714.9
5°	7646.4
7.5°	7479.8
10°	7180.7
12.5°	6817.6
15°	6397.5
17.5°	5954.6
20°	5415.7
22.5°	4929.4
25°	4440.8
27.5°	3920.2
30°	3338.0
32.5°	2650.8
35°	1801.4
37.5°	1157.6
40°	758.0
42.5°	495.5
45°	294.5
47.5°	164.4
50°	84.5
52.5°	38.8
55°	22.8
57.5°	18.3
60°	13.7
62.5°	11.4
65°	9.1
67.5°	6.8
70°	6.8
72.5°	6.8
75°	6.8
77.5°	4.6
80°	2.3
82.5°	2.3
85°	2.3
87.5°	0.0
90°	0.0

(END OF REPORT)