

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573908

Luminaire Tested: **FLD6C-02-D010 FEU6C-X-90-30 F6X-W-X-H**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573908
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6C-02-D010 FEU6C-X-90-30 F6X-W-X-H
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 6LBWH TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 297.0 lumens
Efficiency: N/A
Efficacy: 84.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 3.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573908

CATALOG NUMBER: FLD6C-02-D010 FEU6C-X-90-30 F6X-W-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P573908

CATALOG NUMBER: FLD6C-02-D010 FEU6C-X-90-30 F6X-W-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91			91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			81
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73			73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			65
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59			59
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			53
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49			49
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41			41
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	10043
5°	10037
10°	9959
15°	9892
20°	9743
25°	9521
30°	8963
35°	8111
40°	6777
45°	5194
50°	3676
55°	2322
60°	1305
65°	843
70°	561
75°	402
80°	253
85°	252



TEST NUMBER: P573908

CATALOG NUMBER: FLD6C-02-D010 FEU6C-X-90-30 F6X-W-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	17.3	5.8
10°-20°	49.1	16.5
20°-30°	72.0	24.2
30°-40°	74.9	25.2
40°-50°	51.8	17.5
50°-60°	22.6	7.6
60°-70°	6.9	2.3
70°-80°	2.1	0.7
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	138.4	46.6
0°-40°	213.3	71.8
0°-60°	287.7	96.9
0°-90°	297.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	297.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	183	
5°	182	17
15°	174	49
25°	157	72
35°	121	75
45°	67	52
55°	24	23
65°	6	7
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P573908

CATALOG NUMBER: FLD6C-02-D010 FEU6C-X-90-30 F6X-W-X-H

CANDELA DISTRIBUTION (FULL):

0°	
0°	183.2
2.5°	183.6
5°	182.4
7.5°	180.9
10°	178.9
12.5°	177.0
15°	174.3
17.5°	170.9
20°	167.0
22.5°	162.8
25°	157.4
27.5°	150.5
30°	141.6
32.5°	132.4
35°	121.2
37.5°	108.9
40°	94.7
42.5°	80.4
45°	67.0
47.5°	54.3
50°	43.1
52.5°	32.7
55°	24.3
57.5°	17.3
60°	11.9
62.5°	8.9
65°	6.5
67.5°	5.0
70°	3.5
72.5°	2.7
75°	1.9
77.5°	1.1
80°	0.8
82.5°	0.4
85°	0.4
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)