

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366574

Luminaire Tested: **FLD6BX70D010TE-FEU6B67-8040-F6LBXVM1-WMH-BTR85**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P366574
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-30)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX70D010TE-FEU6B67-8040-F6LBXVM1-WMH-BTR85
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, WARM HAZE REFLECTOR,
BOTTOM TRIM POLYCARBONATE, CLEAR 0.187", 7000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5348.0 lumens
Efficiency: N/A
Efficacy: 72.9 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.8
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 73.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P366574

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8040-F6LBXVM1-WMH-BTR85

Luminous Intensity Polar Plot





TEST NUMBER: P366574

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8040-F6LBXVM1-WMH-BTR85

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	92	90	88
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	84	83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	80	78
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74
6	90	82	76	72	89	81	76	72	80	75	72	78	74	71	77	74	71	69
7	86	78	72	68	85	77	72	68	76	71	68	75	70	67	73	70	67	66
8	82	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62
9	79	70	64	61	78	69	64	61	69	64	60	68	63	60	67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	552924
5°	543823
10°	518171
15°	473498
20°	406054
25°	325812
30°	228433
35°	105539
40°	33883
45°	10936
50°	5080
55°	4494
60°	4468
65°	4066
70°	4020
75°	4648
80°	5938
85°	9858



TEST NUMBER: P366574

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8040-F6LBXVM1-WMH-BTR85

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	709.6	13.3
10°-20°	1767.6	33.1
20°-30°	1856.3	34.7
30°-40°	823.7	15.4
40°-50°	106.4	2.0
50°-60°	33.3	0.6
60°-70°	23.4	0.4
70°-80°	17.1	0.3
80°-90°	10.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
<hr/>		
0°-30°	4333.5	81.0
0°-40°	5157.3	96.4
0°-60°	5297.0	99.0
0°-90°	5348.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5348.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7722	
5°	7566	710
15°	6388	1768
25°	4124	1856
35°	1207	824
45°	108	106
55°	36	33
65°	24	23
75°	17	17
85°	12	10
90°	0	



TEST NUMBER: P366574

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8040-F6LBXVM1-WMH-BTR85

CANDELA DISTRIBUTION (FULL):

0°	
0°	7722.2
2.5°	7674.2
5°	7566.2
7.5°	7419.8
10°	7126.9
12.5°	6798.1
15°	6387.6
17.5°	5895.5
20°	5329.0
22.5°	4733.7
25°	4124.0
27.5°	3439.8
30°	2762.9
32.5°	2030.8
35°	1207.4
37.5°	643.3
40°	362.5
42.5°	199.2
45°	108.0
47.5°	55.2
50°	45.6
52.5°	40.8
55°	36.0
57.5°	33.6
60°	31.2
62.5°	26.4
65°	24.0
67.5°	19.2
70°	19.2
72.5°	16.8
75°	16.8
77.5°	14.4
80°	14.4
82.5°	12.0
85°	12.0
87.5°	7.2
90°	0.0

(END OF REPORT)