

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365862

Luminaire Tested: **FLD6BX70D010TE-FEU6B67-8050-F6LBXVM1-MW-BL85**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365862
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-37)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX70D010TE-FEU6B67-8050-F6LBXVM1-MW-BL85
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, MATTE WHITE REFLECTOR, BOTTOM LENS POLYCARBONATE, CLEAR 0.187", 7000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5684.0 lumens
Efficiency: N/A
Efficacy: 77.4 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.95
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 73.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365862

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8050-F6LBXVM1-MW-BL85

Luminous Intensity Polar Plot





TEST NUMBER: P365862

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8050-F6LBXVM1-MW-BL85

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97		98	96	94		95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86		90	87	84		87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76		82	78	75		80	77	74	72
4	91	82	75	69	89	80	74	69	78	73	68		76	71	67		74	70	67	65
5	85	75	68	63	83	74	67	62	72	66	62		70	65	61		69	64	60	59
6	80	69	62	57	78	68	62	57	67	61	56		65	60	56		64	59	55	54
7	75	64	57	52	74	63	57	52	62	56	51		61	55	51		60	55	51	49
8	71	60	53	48	70	59	52	48	58	52	47		57	51	47		56	51	47	45
9	67	56	49	44	66	55	49	44	54	48	44		53	48	44		52	47	44	42
10	64	52	46	41	62	52	45	41	51	45	41		50	45	41		49	44	41	39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	125828
5°	123048
10°	116705
15°	109385
20°	102068
25°	93877
30°	80423
35°	61230
40°	44975
45°	34075
50°	27906
55°	24545
60°	21929
65°	19222
70°	16428
75°	12812
80°	8573
85°	3886



TEST NUMBER: P365862

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8050-F6LBXVM1-MW-BL85

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	419.4	7.4
10°-20°	1085.9	19.1
20°-30°	1415.1	24.9
30°-40°	1153.7	20.3
40°-50°	698.4	12.3
50°-60°	463.9	8.2
60°-70°	296.7	5.2
70°-80°	131.5	2.3
80°-90°	19.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2920.3	51.4
0°-40°	4074.0	71.7
0°-60°	5236.3	92.1
0°-90°	5684.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5684.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4606	
5°	4488	419
15°	3868	1086
25°	3115	1415
35°	1836	1154
45°	882	698
55°	515	464
65°	297	297
75°	121	131
85°	12	20
90°	0	



TEST NUMBER: P365862

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8050-F6LBXVM1-MW-BL85

CANDELA DISTRIBUTION (FULL):

0°	
0°	4606.5
2.5°	4571.8
5°	4487.6
7.5°	4361.2
10°	4207.6
12.5°	4039.1
15°	3868.1
17.5°	3697.1
20°	3511.3
22.5°	3332.8
25°	3114.8
27.5°	2862.0
30°	2549.8
32.5°	2193.0
35°	1836.2
37.5°	1514.0
40°	1261.3
42.5°	1045.7
45°	882.1
47.5°	753.3
50°	656.7
52.5°	577.4
55°	515.4
57.5°	455.9
60°	401.4
62.5°	349.4
65°	297.4
67.5°	250.3
70°	205.7
72.5°	161.1
75°	121.4
77.5°	86.7
80°	54.5
82.5°	29.7
85°	12.4
87.5°	2.5
90°	0.0

(END OF REPORT)