

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P576358

Luminaire Tested: **FLD6C-25-D010 FEU6C-X-90-35 F6X-N-X-LI**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P576358
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6C-25-D010 FEU6C-X-90-35 F6X-N-X-LI
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 6LBNLI TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2062.0 lumens
Efficiency: N/A
Efficacy: 65.5 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P576358

CATALOG NUMBER: FLD6C-25-D010 FEU6C-X-90-35 F6X-N-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P576358

CATALOG NUMBER: FLD6C-25-D010 FEU6C-X-90-35 F6X-N-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | |
| 1 | 114 | 112 | 109 | 107 | 112 | 109 | 107 | 106 | 105 | 104 | 102 | 102 | 101 | 99 | 98 | 97 | 96 | 95 | | | |
| 2 | 109 | 105 | 101 | 98 | 107 | 103 | 100 | 97 | 100 | 97 | 95 | 97 | 95 | 93 | 94 | 93 | 91 | 89 | | | |
| 3 | 105 | 99 | 94 | 91 | 103 | 97 | 93 | 90 | 95 | 91 | 89 | 93 | 90 | 87 | 90 | 88 | 86 | 85 | | | |
| 4 | 100 | 93 | 88 | 85 | 98 | 92 | 88 | 84 | 90 | 86 | 83 | 88 | 85 | 82 | 86 | 84 | 81 | 80 | | | |
| 5 | 96 | 88 | 83 | 79 | 94 | 87 | 83 | 79 | 86 | 82 | 78 | 84 | 81 | 78 | 83 | 80 | 77 | 76 | | | |
| 6 | 92 | 84 | 79 | 75 | 90 | 83 | 78 | 75 | 82 | 77 | 74 | 80 | 76 | 74 | 79 | 76 | 73 | 72 | | | |
| 7 | 88 | 80 | 74 | 71 | 87 | 79 | 74 | 71 | 78 | 73 | 70 | 77 | 73 | 70 | 76 | 72 | 69 | 68 | | | |
| 8 | 84 | 76 | 71 | 67 | 83 | 75 | 70 | 67 | 74 | 70 | 67 | 73 | 69 | 66 | 73 | 69 | 66 | 65 | | | |
| 9 | 81 | 73 | 67 | 64 | 80 | 72 | 67 | 64 | 71 | 67 | 63 | 70 | 66 | 63 | 70 | 66 | 63 | 62 | | | |
| 10 | 78 | 69 | 64 | 61 | 77 | 69 | 64 | 61 | 68 | 64 | 61 | 67 | 63 | 60 | 67 | 63 | 60 | 59 | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 257364 |
| 5° | 240677 |
| 10° | 196295 |
| 15° | 144445 |
| 20° | 99560 |
| 25° | 73916 |
| 30° | 55521 |
| 35° | 34619 |
| 40° | 16803 |
| 45° | 5768 |
| 50° | 759 |
| 55° | 573 |
| 60° | 329 |
| 65° | 389 |
| 70° | 481 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |



TEST NUMBER: P576358

CATALOG NUMBER: FLD6C-25-D010 FEU6C-X-90-35 F6X-N-X-LI

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 390.3 | 18.9 |
| 10°-20° | 700.6 | 34.0 |
| 20°-30° | 566.5 | 27.5 |
| 30°-40° | 326.3 | 15.8 |
| 40°-50° | 69.0 | 3.3 |
| 50°-60° | 6.0 | 0.3 |
| 60°-70° | 3.0 | 0.1 |
| 70°-80° | 0.4 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1657.4 | 80.4 |
| 0°-40° | 1983.7 | 96.2 |
| 0°-60° | 2058.7 | 99.8 |
| 0°-90° | 2062.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 2062.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 4695 | |
| 5° | 4374 | 390 |
| 15° | 2545 | 701 |
| 25° | 1222 | 566 |
| 35° | 517 | 326 |
| 45° | 74 | 69 |
| 55° | 6 | 6 |
| 65° | 3 | 3 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P576358

CATALOG NUMBER: FLD6C-25-D010 FEU6C-X-90-35 F6X-N-X-LI

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 4694.7 |
| 2.5° | 4638.3 |
| 5° | 4373.6 |
| 7.5° | 3993.0 |
| 10° | 3526.3 |
| 12.5° | 3047.6 |
| 15° | 2545.1 |
| 17.5° | 2060.5 |
| 20° | 1706.6 |
| 22.5° | 1436.1 |
| 25° | 1222.0 |
| 27.5° | 1040.7 |
| 30° | 877.1 |
| 32.5° | 695.8 |
| 35° | 517.3 |
| 37.5° | 359.7 |
| 40° | 234.8 |
| 42.5° | 142.7 |
| 45° | 74.4 |
| 47.5° | 29.7 |
| 50° | 8.9 |
| 52.5° | 8.9 |
| 55° | 6.0 |
| 57.5° | 6.0 |
| 60° | 3.0 |
| 62.5° | 3.0 |
| 65° | 3.0 |
| 67.5° | 3.0 |
| 70° | 3.0 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)