

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366597

Luminaire Tested: **FLD6BX70D010TE-FEU6B67-8050-F6LBXVM1-WMH-BTR94**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P366597
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-33)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX70D010TE-FEU6B67-8050-F6LBXVM1-WMH-BTR94
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, WARM HAZE REFLECTOR,
BOTTOM TRIM GLASS, TEMPERED CLEAR 0.187", 7000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5609.0 lumens
Efficiency: N/A
Efficacy: 76.4 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.8
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 73.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P366597

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8050-F6LBXVM1-WMH-BTR94

Luminous Intensity Polar Plot





TEST NUMBER: P366597

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8050-F6LBXVM1-WMH-BTR94

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	92	90	88
3	104	98	93	89	102	96	92	88	94	90	87	91	88	86	89	87	84	83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78
5	94	87	81	77	93	86	81	77	84	80	76	82	78	75	81	77	75	73
6	90	82	76	72	89	81	76	72	80	75	72	78	74	71	77	73	71	69
7	86	78	72	68	85	77	72	68	76	71	67	74	70	67	73	70	67	65
8	82	74	68	64	81	73	68	64	72	67	64	71	67	63	70	66	63	62
9	79	70	64	61	78	69	64	61	68	64	60	68	63	60	67	63	60	59
10	76	66	61	57	75	66	61	57	65	61	57	65	60	57	64	60	57	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	576825
5°	570302
10°	541416
15°	493053
20°	424326
25°	339954
30°	239834
35°	111080
40°	36117
45°	11544
50°	5514
55°	4943
60°	4611
65°	4202
70°	4145
75°	5478
80°	6144
85°	10187



TEST NUMBER: P366597

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8050-F6LBXVM1-WMH-BTR94

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	741.4	13.2
10°-20°	1844.6	32.9
20°-30°	1946.7	34.7
30°-40°	871.1	15.5
40°-50°	114.0	2.0
50°-60°	35.1	0.6
60°-70°	24.8	0.4
70°-80°	19.6	0.3
80°-90°	11.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4532.8	80.8
0°-40°	5403.9	96.3
0°-60°	5553.0	99.0
0°-90°	5609.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5609.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8056	
5°	7935	741
15°	6651	1845
25°	4303	1947
35°	1271	871
45°	114	114
55°	40	35
65°	25	25
75°	20	20
85°	12	11
90°	0	



TEST NUMBER: P366597

CATALOG NUMBER: FLD6BX70D010TE-FEU6B67-8050-F6LBXVM1-WMH-BTR94

CANDELA DISTRIBUTION (FULL):

	0°
0°	8056.0
2.5°	8003.9
5°	7934.6
7.5°	7738.9
10°	7446.6
12.5°	7097.3
15°	6651.4
17.5°	6155.9
20°	5568.8
22.5°	4971.8
25°	4303.0
27.5°	3626.7
30°	2900.8
32.5°	2150.2
35°	1270.8
37.5°	691.1
40°	386.4
42.5°	215.5
45°	114.0
47.5°	59.5
50°	49.5
52.5°	42.1
55°	39.6
57.5°	34.7
60°	32.2
62.5°	27.2
65°	24.8
67.5°	22.3
70°	19.8
72.5°	19.8
75°	19.8
77.5°	17.3
80°	14.9
82.5°	14.9
85°	12.4
87.5°	7.4
90°	0.0

(END OF REPORT)