

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P574728

Luminaire Tested: **FLD6C-10-D010 FEU6C-X-90-27 F6X-N-X-H**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P574728
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6C-10-D010 FEU6C-X-90-27 F6X-N-X-H
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 2700K, 90 CRI LEDS, 6LBNH TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 623.0 lumens
Efficiency: N/A
Efficacy: 63.9 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 9.75
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P574728

CATALOG NUMBER: FLD6C-10-D010 FEU6C-X-90-27 F6X-N-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P574728

CATALOG NUMBER: FLD6C-10-D010 FEU6C-X-90-27 F6X-N-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	43779
5°	42697
10°	39395
15°	34881
20°	30283
25°	25907
30°	21358
35°	14067
40°	7557
45°	3349
50°	1356
55°	975
60°	625
65°	441
70°	369
75°	233
80°	347
85°	0



TEST NUMBER: P574728

CATALOG NUMBER: FLD6C-10-D010 FEU6C-X-90-27 F6X-N-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.8	11.5
10°-20°	171.3	27.5
20°-30°	196.2	31.5
30°-40°	131.8	21.2
40°-50°	37.7	6.0
50°-60°	9.2	1.5
60°-70°	3.5	0.6
70°-80°	1.3	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	439.3	70.5
0°-40°	571.1	91.7
0°-60°	618.0	99.2
0°-90°	623.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	623.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	799	
5°	776	72
15°	615	171
25°	428	196
35°	210	132
45°	43	38
55°	10	9
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P574728

CATALOG NUMBER: FLD6C-10-D010 FEU6C-X-90-27 F6X-N-X-H

CANDELA DISTRIBUTION (FULL):

	0°
0°	798.6
2.5°	793.0
5°	775.9
7.5°	745.2
10°	707.7
12.5°	660.0
15°	614.6
17.5°	566.9
20°	519.1
22.5°	473.7
25°	428.3
27.5°	386.2
30°	337.4
32.5°	272.6
35°	210.2
37.5°	153.4
40°	105.6
42.5°	69.3
45°	43.2
47.5°	26.1
50°	15.9
52.5°	12.5
55°	10.2
57.5°	8.0
60°	5.7
62.5°	4.5
65°	3.4
67.5°	2.3
70°	2.3
72.5°	1.1
75°	1.1
77.5°	1.1
80°	1.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)